

# UNIVERSAL SOCKET CHARGING ADAPTER (2 x USB-A)



Manual DA-70617

### Description

Power supply: 16A, 250V, 50Hz

Protection class: IP 20

USB: 2x Type A
Output: 5V 2.1A total

## Specification

Mains/power socket/plug: Max. Input current: 16A

Rated voltage: 250V 50Hz
Rated power max: 3680W

Input voltage: 100-250v

**Environment:** 

Working temp: 0 °C - 35 °C

#### **Energy Efficiency**

- Input: 250V~, 50 Hz, Max 0.2A
- Output: 5.0Vd.c. 2.4A, Max. 12.0W,
- Average active efficiency = 80.0%
- Efficiency at low load (10 %) = 71.2%
- No-load power consumption = 0.09

#### **USB Charger**

- 2x USB connector (A&A)
- Charger for mobile devices (e.g. smartphone, tablet, etc.)

#### How to link power

- Install the USB plug adapter by connecting it to a grounded power outlet,
- The indicator or the charge control light will now turn red. The device is ready for operation.
- Up to 2 suitable USB devices can now be connected via the USB ports by using USB connection cable.
- At the same time suitable household appliances can be connected and put into operation via the socket outlet

#### Safety precautions

- Please read this manual thoroughly before first use and keep it in a safe place for future reference.
- The safety precautions enclosed herein reduce the risk of fire, electric shock and injury when correctly adhered to. The power plug is designed for private

- use. It is not suitable for commercial use. The device is not designed for outdoor usage.
- The units can only be operated individually. Do not plug the charging adapter one behind the other.
- · Any other use is considered improper.
- Children do not recognize the danger of improper use of electrical equipment.
- Let them never use electrical appliances unattended.
- Danger of suffocation! Do not leave packaging material lying carelessly. Children can swallow small parts and suffocate
- The power plug can only be used in conventional earthed sockets with an alternating voltage of 90 ~ 240V and 50Hz
- Use of the power plug only in permanently installed wall sockets
- Do not plug the switch sockets into an extension cable
- Make sure that the plug of a device is completely plugged into the power plug
- The outlet must be located close to the device and easily accessible

- Do not connect loads whose unattended switching on could cause a fire (e.g. an iron) or other hazards
- Heaters and similar devices should never be unattended during use
- Do not connect loads that require a motor capacitor (e.g. a refrigerator)
- Only use the charging adapter within the specified temperature range between 0  $^{\sim}$  40  $^{\circ}$ C
- When not in use, store the product in a clean and dry place in temperatures between 0°C and 40°C
- · Do not exceed the maximum power rating 3680 W
- Do not cover the power plug. Heat is accumulating under the cover. There is a fire hazard
- Do not let the devices come into contact with liquids
- · Do not touch the power plug with wet hands
- Ensure that the devices are only used inside. These devices are not intended for outdoor use and can be damaged.
- Install the power plug in close proximity to an easily accessible wall outlet.

- Never try to repair the power plug by yourself.
   Repair and maintenance work must be carried out by specialists. Check the units regularly for damage.
   Do not use the power plugs if there is obvious damage to the housing
- · In case of problems contact our customer service
- To disconnect the power plug, disconnect from the mains
- If the power plug needs cleaning, disconnect it from the main power and wipe the outlet with a dry cloth

Hereby Assmann Electronic GmbH declares that the Declaration of Conformity is part of the shipping content. If the Declaration of Conformity is missing, you can request it by post under the below mentioned manufacturer address.

www.assmann.com Assmann Electronic GmbH Auf dem Schüffel 3 58513 Lüdenscheid Germany

