
SAUTER **CP 1500-0Y4**

Single-point load cell made of anodised aluminium



Category

Brand	Sauter
Product categoriy	Measuring cell
Product group	Load cell
Product family	CP Y4

Measuring System

Weighing capacity [Max]	1,5 kg
Load cell - characteristic value - nominal	0,9 mV/V
Load cell - characteristic value - variance	0,1 mV/V
Load cell OIML class	C3
Load cell connection	4-wire
Power supply + Colour	red
Power supply - Colour	black
Signal + Colour	green
Signal - Colour	white
Load cell - Resolution (verifiable)	3000 e
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Directions of force	compression
Load sell - Input resistance - nominal	405 Ω
Load cell - Input resistance - variance	6 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Output resistance - variance	3 Ω
Load cell - Recommended exitation voltage [Min]	9 V
Load cell - Recommended exitation voltage [Max]	12 V
Load cell - Isolation resistance - [Min]	5000 MΩ
Load cell - Combined error	0,017%
Temperature coefficient - characteristic value	± 0.02% F.S. /10 °C
Zero balance	≤± 1.0%FS
Temperature coefficient - zero signal	± 0.02% F.S. /10 °C
Creep error (30 minutes)	± 0.03% F.S.
Safe overload	120%
Ultimate overload	150%

Functions

IP protection - complete device	IP65

Construction

Material	aluminium
Design	Singlepoint load cell
Dimension (W×D×H)	110×33×10 mm
Cable length	0,45 m
Mounting - force application	2 × threaded hole M3
Mounting - force dissipation	2 × threaded hole M3

Environmental conditions

Ambient temperature [Min]	-20 °C
Ambient temperature [Max]	50 °C
Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Storage temperature [Min]	-30 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓

Product information

GTIN/EAN number	4045761242272
REACH classification	no prohibited substances

Packing & Shipping

Shipping method	Parcel service
Delivery time	1 d
Dimensions packaging (W×D×H)	120×50×35 mm
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg

SAUTER **CP 1500-0Y4**

Single-point load cell made of anodised aluminium

Pictograms

STANDARD



OPTION

