


5-Port Industrial Fast Ethernet DIN-Rail Switch

TI-E50 (v1.0R)


- 5 x Fast Ethernet ports
- 1Gbps switching capacity
- Hardened IP30 rated metal switch
- Includes DIN-Rail mount and wall mount brackets
- Wide operating temperature range of -40° – 75° C (-40° – 167° F)
- Dual inputs provide redundant power with overload current protection
- Power supply sold separately (model: TI-M6024)
- Fanless design for silent operation
- Lifetime Warranty

TRENDnet's Industrial Fast Ethernet DIN-Rail Switches feature a rugged IP30 rated metal enclosure. These industrial Ethernet switches are designed to withstand high levels of vibration and shock, operate in both low and high temperatures for industrial environments within a -40° – 75° C (-40° – 167° F) wide-temperature range. Redundant power inputs with overload current protection on each industrial Ethernet switch minimizes network downtime.




Easy Installation

No configuration needed, simply connect network devices to the industrial Ethernet switch.



Redundant Power




The industrial Ethernet switches feature dual power inputs to provide redundant power with overload current protection.



Industrial Hardened Design

Equipped with a rugged IP30 rated housing, and designed to withstand a high degree of vibration and shock, while operating within a wide temperature range of -40° – 75° C (-40° – 167° F).

NETWORKING SOLUTION



FEATURES



Easy Installation

Industrial Ethernet switches feature a quick and easy installation process with an intuitive guided setup



DIN-Rail / Wall Mounts

IP30 rated metal enclosure with DIN-Rail mount and wall mount hardware included



Shock and Vibration Resistant

Rated for shock (EN 60068-2-27), freefall (EN 60068-2-32), and vibration (EN 60068-2-6)



Wide Temperature Range

A wide operating temperature range of -40° – 75° C (-40° – 167° F) allows for installations in industrial environments with extreme hot or cold conditions



Redundant Power

Dual power inputs provide redundant power with overload current protection (power supply sold separately, model: TI-M6024)



Electro Magnetic Compliance

Complies with industrial EMS certifications (IEC 61000-4-2) ESD: Contact: 6kV | Air: 8kV, (IEC 61000-4-4) EFT: Power: 2kV | Signal: 2kV, (61000-4-5) Surge: Power: 2kV | Signal: 2kV



Grounding Point

Grounding point on each industrial Ethernet switch designed to protect equipment from external electrical surges

SPECIFICATIONS

Standards

- IEEE 802.3
- IEEE 802.3u
- IEEE 802.3ab
- IEEE 802.3x

Device Interface

- 5 x Fast Ethernet ports
- 4-pin removable terminal block
- LED indicators
- Wall mount
- DIN-Rail mount
- Grounding point

Data Transfer Rate

- Ethernet: 10Mbps (half duplex), 20Mbps (full duplex)
- Fast Ethernet: 100Mbps (half duplex), 200Mbps (full duplex)

Performance

- Data RAM Buffer: 56KB (change unit of measure)
- Switching Fabric: 1Gbps
- MAC Address Table: 1K entries
- Forwarding rate: 0.744Mpps (64-byte packet size)

Special Features

- Hardened components rated for extreme temperatures
- Redundant power inputs
- ESD 8kV support
- Low-profile design

DC Power

- Input: 12 – 56V DC
- Recommended power supply: TI-M6024 (sold separately)
- Max. consumption: 2.24W

Terminal Block

- Redundant power inputs, 4-pin
- Wire range: 0.34mm² to 2.5mm²
- Solid wire (AWG): 12-24/14-22
- Stranded wire (AWG): 12-24/14-22
- Torque: 5 lb. – in. / 0.5Nm / 0.56Nm
- Wire strip length: 7-8mm

MTBF

- 510,304 hours

Housing

- IP30 metal case
- DIN-Rail mount
- Wall mount
- Grounding point

Operating Temperature

- -40° – 75° C (-40° – 167° F)

Operating Humidity

- Max. 95% non-condensing

Dimensions

- 104 x 82 x 32mm (4 x 3.2 x 1.25 in.)

Weight

- 486g (17.1 oz.)

Certifications

- CE
- FCC
- Shock (IEC 60068-2-27)
- Freefall (IEC 60068-2-32)
- Vibration (IEC 60068-2-6)
- IEC 61000-4-2
- IEC 61000-4-4
- IEC 61000-4-5

Warranty

- Lifetime

Package Contents

- TI-E50
- Quick Installation Guide
- Removable terminal block
- DIN-Rail and wall mount kit

TRENDnet offers a lifetime warranty for all of its metal-enclosed network switches that have been purchased in the United States/Canada on or after 1/1/2015. Cooling fan and internal power supply carry a one-year warranty.

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.