


SBC-LCD01

1.3-Inch HD IPS TFT LCD



This IPS TFT display is controlled via SPI. This makes it suitable for use as an output device for micro-controllers (e.g. NodeMCU) and single-board computers (e.g. Raspberry Pi). By using a high-resolution IPS panel with a pixel density of over 260 PPI, content can be displayed in high-resolution on the compact display.

MAIN FEATURES


Type	Full color IPS TFT-LCD
Resolution	240 x 240 Pixel
Control chip	ST7789VW
Interfaces	SPI
Dimensions	30 x 27 x 10 mm
Items delivered	SBC-LCD01

FURTHER SPECIFICATIONS

Supply voltage	3.3 V
Supply current	8 - 10 mA
Logic level voltage	3.3 V
Brightness	300- 350 cd/m ²
Contrast	640-800 : 1
Response time	30-35 ms
Operation temperature	-20 °C - 70 °C

FURTHER DETAILS

Article No.	SBC-LCD01
EAN:	4250236820330
Customs Tariff No.	8473302000



Published: 29.09.2020