

COM-OLED16X2

Character OLED with 2 lines each 16 characters



Due to the OLED technology, this display has a high contrast and brightness, as well as a viewing angle of over 175°.

By means of its interfaces, it provides a wide range of applications: The interfaces can be selected by re-soldering resistors on the back of the board. There is a serial interface (which can be used with SPI) and two parallel interfaces (8080 / 6800).

The design is compatible with displays frequently used in the industry - with minor changes in the software, these can then be upgraded with OLED technology.

MAIN FEATURES	
Туре	OLED
Resolution	16 x 2 characters (each 5 x 8 dots or 5x 10 dots per character), total 100 x 16 pixel
Background-/ display color	blue on black
Control chip	IST0010
Interfaces	SPI (8bit serial); 16 Pins
Special features	High contrast; bright, wide viewing angle
Dimensions	80 x 36 x 10 mm
Items delivered	COM-OLED16x2, a pin bar

FURTHER SPECIFICATIONS	
Voltage supply	3 - 5 V
Supply current	31 mA
Logic level	$0.2 * V_{DD} - V_{DD}$
Brightness	typ. 100-120 cd/m ²
Contrast	2000:1
Viewing angle	> 175°
Operating temperature	- 40 ° C - 80 ° C
Preinstalled fonts	English, German, Russian, Japanese

FURTHER DETAILS	
Article No.	COM-OLED16x2
EAN:	4250236820293
Customs tariff No.	8473302000

Published: 05.03.2021