

KERN SFB 60K-2XLM

KERN

Stainless steel platform scale with IP65/IP67 protection and XL platform, verification optional



Category

Brand	KERN
Product category	Industrial scale
Product group	Stainless steel platform scale
Product family	SFB

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	60 kg
Readability [d]	0,02 kg
Reproducibility	0,02 kg
Linearity	± 0,02 kg
Minimum weight [Min]	0,4 kg
Conformity assessment possible	✓
Resolution	3.000
Tare range	-60 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (M1)
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,02 kg
Load cell connection	6-wire
Construction type of the scale	Single-range balance
Units	kg
Default unit	kg
Loadcell type	stainless steel IP67 silicone-coated

Display

Display type	LCD
--------------	-----

Display type	LCD with backlight
Display backlight	✓
Display segments	5 + 1/2
Display digit height	52 mm
Languages of the user interface	Symbol language

Construction

Dimensions completely mounted (W×D×H)	500×560×590 mm
Dimension display device (W×D×H)	266×165×96 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×120 mm
Material weighing plate	stainless steel
Material platform	stainless steel
Material display housing	stainless steel
Material load cell(s)	stainless steel
Level indicator	✓
Levelling feet adjustable	✓
Wall mount	✓
Cable length	3 m
Display device cable length	3 m
Allowed cable length display device [Max]	30 m

Functions

Sum memory function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Reference quantity	10, 20, 50, 100, 200
IP protection - display	IP65
IP protection - platform	no IP protection
IP protection - load cell	IP67
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Auto-off interval(s) in mains power mode	selectable free
Tare function	manual (single & multi)
Number of keys for operation	7

KERN SFB 60K-2XLM

KERN

Stainless steel platform scale with IP65/IP67 protection and XL platform, verification optional

Interface

Interfaces	RS-232 (optional, factory) Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory)
------------	---

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US
Input voltage power supply / power [Max]	110 V - 230 V AC
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 500 mA
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
Battery / accumulator type	Pb
Battery connection	Plug-in terminals
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	35 h
Rechargeable battery charging time	12 h
Battery/Accu connected	fixed electrical connection, not insulated

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	95 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Conformity assessment possible ex works ✓

Accuracy classe	III
Verification scale interval [e]	0,02 kg

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129
Article number for certificate of conformity	969-517

Packing & Shipping


Delivery time	1 d
Dimensions packaging (W×D×H)	555×940×220 mm
Shipping method	Parcel service
Net weight approx.	14 kg
Gross weight approx.	19 kg
Shipping weight	23 kg

Product information

GTIN/EAN number	4045761247932
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

DAkkS

FACTORY

