

# AC/DC/IR/GB

# Electrical Safety Analyzer



## GPT-12000 Series

### AC/DC/IR/GB Electrical Safety Analyzer

- 200VA AC Test Capacity
- 7" LCD Color Display
- Capacitive Load Testing Capability Up to  $47\mu F$
- Controllable Ramp Up & Ramp Down Time
- Statistic Function
- Testing Time Starting From 0.3s
- Provide USB Flash Drive Storage Function
- Universal Power Input

NEW



Function MODEL	Output Capacity	AC	DC	IR	GB	Continuity	Rear Output
GPT-12001	200VA	✓				✓	✓
GPT-12002	200VA	✓	✓			✓	✓
GPT-12003	200VA	✓	✓	✓		✓	✓
GPT-12004	200VA	✓	✓	✓	✓	✓	✓

[www.gwinstek.com](http://www.gwinstek.com)

**GW INSTEK**  
Simply Reliable

## SPECIFICATIONS

AC WITHSTANDING	
Output-Voltage Range	0.050kV~5.000kV
Output-Voltage Resolution	1V
Output-Voltage Accuracy	$\pm(1\% \text{ of setting} + 5V)$ [no load]
Maximum Rated Load	200 VA (5kV/40mA)
Maximum Rated Current	40mA (0.5kV < V $\leq$ 5kV); 10mA (0.05kV $\leq$ V $\leq$ 0.5kV)
Output-Voltage Waveform	Sine wave
Output-Voltage Frequency	50 Hz / 60 Hz selectable
Voltage Regulation	$\pm(1\% + 5V)$ [maximum rated load -- no load]
Voltmeter Accuracy	$\pm(1\% \text{ of reading} + 5V)$
Current Measurement Range	1μA~40.00mA
Current Best Resolution	1μA / 10μA
Current Measurement Accuracy	$\pm(1.5\% \text{ of reading} + 30\mu A)$
Window Comparator Method	Yes
ARC Detect	Yes
RAMP UP (Rise Time)	0.1s~999.9s
RAMP DOWN (Fall Time)	0.0s~999.9s
TIMER (Test Time)	OFF, 0.3s~999.9s
WAIT TIME	0.0s~999.9s
GND	ON/OFF
DC WITHSTANDING	
Output-Voltage Range	0.050kV~6.000kV
Output-Voltage Resolution	1V
Output-Voltage Accuracy	$\pm(1\% \text{ of setting} + 5V)$ [no load]
Maximum Rated Load	50W (5kV/10mA)
Maximum Rated Current	10mA (0.5kV < V $\leq$ 6kV); 2mA (0.05kV $\leq$ V $\leq$ 0.5kV)
Voltage Regulation	$\pm(1\% + 5V)$ [maximum rated load -- no load]
Voltmeter Accuracy	$\pm(1\% \text{ of reading} + 5V)$
Current Measurement Range	1μA~10.00mA
Current Best Resolution	1μA / 1μA / 10μA
Current Measurement Accuracy	$\pm(1.5\% \text{ of reading} + 3\mu A)$ when I Reading < 1mA ; $\pm(1.5\% \text{ of reading} + 30\mu A)$ when I Reading $\geq$ 1mA
Window Comparator Method	Yes
ARC Detect	Yes
RAMP UP (Rise Time)	0.1s~999.9s
RAMP DOWN (Fall Time)	0.0s~999.9s
TIMER (Test Time)	OFF, 0.3s~999.9s
WAIT TIME	0.0s~999.9s
GND	ON/OFF
INSULATION RESISTANCE	
Output Voltage	50V~1200V dc
Output-Voltage Resolution	50V
Output-Voltage Accuracy	$\pm(1\% \text{ of setting} + 5V)$ [no load]
Resistance Measurement	Test Voltage      Display Range
	Measurement Range / Accuracy
	50V $\leq$ V $\leq$ 100V      0.1MΩ~10.00GΩ      0.1MΩ~1MΩ : $\pm(5\% \text{ of reading} + 3 \text{ count})$ ; 1 MΩ~50MΩ : $\pm(5\% \text{ of reading} + 1 \text{ count})$ ;
	150V $\leq$ V $\leq$ 450V      0.1MΩ~20.00GΩ      51MΩ~2GΩ : $\pm(10\% \text{ of reading} + 1 \text{ count})$
	500V $\leq$ V $\leq$ 1200V      0.1MΩ~50.00GΩ      0.1MΩ~1MΩ : $\pm(5\% \text{ of reading} + 3 \text{ count})$ ; 1 MΩ~500MΩ : $\pm(5\% \text{ of reading} + 1 \text{ count})$ ; 501MΩ~9.999GΩ : $\pm(10\% \text{ of reading} + 1 \text{ count})$ ; 10GΩ~50GΩ : $\pm(20\% \text{ of reading} + 1 \text{ count})$
Voltage Regulation	$\pm(1\% + 5V)$ [maximum rated load -- no load]
Voltmeter Accuracy	$\pm(1\% \text{ of reading} + 5V)$
Short-Circuit Current	10mA max.
Output Impedance	2kΩ
Window Comparator Method	Yes
RAMP UP (Rise Time)	0.1s~999.9s
RAMP DOWN (Fall Time)	0.0s~999.9s
TIMER (Test Time)	0.3s~999.9s
WAIT TIME	0.0s~999.9s
GND	ON/OFF
GROUND BOND	
Output-Current	0.00A~32.00A ac
Output-Current Resolution	0.01A
Output-Current Accuracy	3A $\leq$ I $\leq$ 18A : $\pm(1\% \text{ of reading} + 0.2A)$ ; 8A $<$ I $\leq$ 32A : $\pm(1\% \text{ of reading} + 0.05A)$
Test-Voltage	8Vac max (open circuit)
Test-Voltage Frequency	50Hz/60Hz selectable
Ohmmeter Measurement Range	1mΩ~ 650mΩ
Ohmmeter Measurement Resolution	0.1mΩ
Ohmmeter Measurement Accuracy	$\pm(1\% \text{ of reading} + 2 m\Omega)$
Window Comparator Method	Yes
TIMER (Test Time)	0.3s~999.9s
Test Method	Four Terminal
GND	ON/OFF
CONTINUITY TEST	
Output-Current	100mA dc (fixed)
Ohmmeter Measurement Range	0.10Ω~ 90.00Ω
Ohmmeter Measurement Resolution	0.01Ω
Ohmmeter Measurement Accuracy	$\pm(10\% \text{ of reading} + 2 m\Omega)$
MEMORY	
Single Step Memory	MANU : 100 blocks
Automatic Testing Memory	AUTO : 100 blocks, Manu per auto : 10
INTERFACE	
Standard (Front)	REMOTE, USB host
Standard (Rear)	Rear Output, RS-232C, USB device, SCAN terminal, Signal I/O,
Option	GPIB
DISPLAY	
	7" color LCD
POWER SOURCE	
	AC 100V~240V $\pm$ 10%, 50Hz/60Hz
DIMENSION & WEIGHT	
	380(W) x 148(H) x 454(D) mm; Approx. 15kg

Specifications subject to change without notice. GPT-12000CD1DH

Global Headquarters  
**GOOD WILL INSTRUMENT CO., LTD.**

T +86-2-2268-0389 F +86-2-2268-0639

China Subsidiary

**GOOD WILL INSTRUMENT (SUZHOU) CO., LTD.**  
T +86-512-6661-7177 F +86-512-6661-7277

Malaysia Subsidiary

**GOOD WILL INSTRUMENT (SEA) SDN. BHD.**  
T +604-6111122 F +604-6115225

Europe Subsidiary

**GOOD WILL INSTRUMENT EURO B.V.**  
T +31(0)40-2557790 F +31(0)40-2541194

U.S.A. Subsidiary  
**INSTEK AMERICA CORP.**

T +1-909-399-3535 F +1-909-399-0819

Japan Subsidiary

**TEXIO TECHNOLOGY CORPORATION.**  
T +81-45-620-2305 F +81-45-534-7181

Korea Subsidiary

**GOOD WILL INSTRUMENT KOREA CO., LTD.**  
T +82-2-3439-2205 F +82-2-3439-2207

**GW INSTEK**

Simply Reliable



[www.gwinstek.com](http://www.gwinstek.com)

[www.facebook.com/GWInsteak](http://www.facebook.com/GWInsteak)