


b/n 2349914 AZ7709T-1AE-6DEF b/n 2349915 AZ7709T-1AE-12DEF b/n 2349916 AZ7709T-1QA-24DEF

### SPST SUBMINIATURE POWER RELAY

#### **FEATURES**

- 4 kV dielectric strength
- Proof tracking index (PTI/CTI) 250
- 5 A switching capability (high capacity version: 10 A)
- Epoxy sealed version available
- UL Class F insulation (155°C) available
- UL. CUR file E365652
- TÜV B 088793 0007





#### **CONTACTS**

Arrangement Ratings (max.)

switched power switched current switched voltage

High cap. version switched power switched current switched voltage SPST (1 Form A) (resistive load)

150 W or 1250 VA

30 VDC\* or 250 VAC

300 W or 2500 VA 10 A 30 VDC\* or 250 VAC

> \* Note: If switching voltage is greater than 30 VDC, special precautions must be taken. Please contact the factory.

Rated Loads UL, CUR

Standard coil

5 A at 250 VAC, resistive, 85°C, 100k cycles [1][2] 5 A at 30 VDC, resistive, 85°C, 100k cycles [1][2] 1/6 HP at 125/250 VAC, 85°C, 100k cycles [1][2]

3 A at 250 VAC, resistive, 85°C, 100k cycles [1][2] 3 A at 30 VDC, resistive, 85°C, 100k cycles [1][2]

High cap. Version - Standard coil

10 A at 250 VAC, resistive, 85°C, 100k cycles [1][2] 10 A at 30 VDC, resistive, 85°C, 100k cycles [1][2] 1/6 HP at 125/250 VAC, 85°C, 100k cycles [1][2] TV-5 at 120 VAC, 25k cycles [1]

High cap. Version - Sensitive coil

8 A at 250 VAC, resistive, 85°C, 100k cycles [1][2] 8 A at 30 VDC, resistive, 85°C, 100k cycles [1][2]

ΤÜV Standard coil

5 A at 250 VAC, resistive, 100k cycles [1]

Sensitive coil

3 A at 250 VAC, resistive, 100k cycles [1]

High cap. Version - Standard coil 10 A at 250 VAC, resistive, 100k cycles [1]

High cap. Version - Sensitive coil

8 A at 250 VAC, resistive, 100k cycles [1]

Contact materials Silver tin oxide [1]

Junkersstr. 3, D-82178 Puchheim, Germany

Silver tin oxide indium oxide [2]

Gold plating available

 $< 100 \text{ m}\Omega$ Initial resistance

**GENERAL DATA** 

Insulation

Life Expectancy (minimum operations)

Mechanical 1 x 10<sup>5</sup> at 5 A 250 VAC resistive Electrical

High cap. version Mechanical

1 x 10<sup>5</sup> at 10 A 250 VAC resistive Electrical

**Operate Time** 8 ms (max.) at nominal coil voltage

**Release Time** 4 ms (max.) at nominal coil voltage, without

coil suppression

**Dielectric Strength** (at sea level for 1 min.)

4000 V<sub>RMS</sub> coil to contact

1000 V<sub>RMS</sub> between open contacts Insulation Resistance

 $1000~\text{M}\Omega$  (min.) at 20°C, 500 VDC, 50% RH (according to DIN VDE 0110, IEC 60664-1)

C250

Overvoltage category: III Pollution degree: 3 Nominal voltage: 250 VAC

Temperature Range

(at nominal coil voltage) -40°C (-40°F) to 85°C (185°F) Operating

Vibration resistance 1.65 mm (0.065") DA at 10-55 Hz

Shock 10 g operating, 100 g damage

**Enclosure** P.B.T. polyester

**Terminals** Tinned copper alloy, P. C.

Soldering 270°C (518°F) Max. Temperature

Max. Time 5 seconds

Cleaning Max. Solvent Temp. 80°C (176°F) Max. Immersion Time 30 seconds

**Dimensions** 

length 18.9 mm (0.718")width 10.7 mm (0.403" (0.618") height 15.7 mm Weight 6 grams (approx.)

Packing unit in pcs 100 per tray / 1000 per carton box UL 508, IEC 61810-1, RoHS, REACH Compliance

ZETTLER electronics GmbH A ZETTLER GROUP Company

> phone: +49 89 800 97-0 fax: +49 89 800 97-200

## **AZ7709**

#### COIL

Nominal coil DC voltages see coil voltage specifications tables

**Dropout** > 5% of nominal coil voltage

Nominal power (approx.) 450 mW standard coil sensitive coil 200 mW Power at pickup voltage (typ.) 220 mW standard coil 113 mW sensitive coil

Max. continuous dissipation 760 mW at 20°C (68°F) ambient

**Temperature Rise** (at nominal coil voltage)

41 K (74°F) 22 K (40°F) standard coil sensitive coil

105°C (221°F) - Class A 155°C (311°F) - Class F Max. temperature

#### **COIL VOLTAGE SPECIFICATIONS**

#### Standard Coil

Nominal Coil VDC	Must Operate VDC	Max. Continuous VDC	Resistance Ohm ± 10%
3	2.1	3.9	20
5	3.5	6.5	55
6	4.2	7.8	80
9	6.3	11.7	180
12	8.4	15.6	320
18	12.6	23.4	720
24	16.8	31.2	1280
48	33.6	62.4	5120


#### **Sensitive Coil**

Nominal Coil VDC	Must Operate VDC	Max. Continuous VDC	Resistance Ohm ± 10%
3	2.25	3.9	45
5	3.75	6.5	125
6	4.5	7.8	180
9	6.75	11.7	400
12	9.0	15.6	720
18	13.5	23.4	1620
24	18.0	31.2	2800

#### **NOTES**

- All values at 20°C (68°F).
- Relay may pull in with less than "Must Operate" value.
- Specifications subject to change without notice.

#### **ORDERING DATA**



Switching capacity nil: standard version T: high capacity version

#### Example ordering data

AZ7709-1AE-12DF

Standard version, silver tin oxide contacts, 12 VDC nominal coil voltage, standard coil, non sealed, non

gold plated, class F insulation system

AZ7709T-1AE-24DSEGF High capacity version, silver tin oxide contacts, 24 VDC

nominal coil voltage, sensitive coil, sealed, gold plated,


class F insulation system


b/n 2349914 AZ7709T-1AE-6DEF b/n 2349915 AZ7709T-1AE-12DEF b/n 2349916 AZ7709T-1QA-24DEF


# **AZ7709**

### **MECHANICAL DATA**

Dimensions in inches with metric equivalents in parentheses. Tolerance: ± .010"








### PC BOARD LAYOUT

Viewed towards terminals



#### **WIRING DIAGRAMS**

Viewed towards terminals

