

GPT-15000 Specifications

The specifications apply when the GPT-15000 is powered on for at least 30 minutes under +15°C~+35°C

GPT-15004 (Front)



GPT-15003/15002/15001 (Front)



GPT-15004 (Rear)



GPT-15003/15002/15001 (Rear)



(All models are available with optional GPIB or LAN)

Model \ Func.	AC Withstanding	DC Withstanding	Insulation Resistance	Ground Bond	Ground Continuity
GPT-15001	√*	----	----	----	√
GPT-15002	√*	√	----	----	√
GPT-15003	√*	√	√	----	√
GPT-15004	√*	√	√	√	√

* : Short current > 200mA

AC WITHSTANDING	
Output-Voltage Range	0.050kV~5.000kV
Output-Voltage Resolution	1V
Output-Voltage Accuracy	± (1% of setting + 5V) [no load]
Maximum Rated Load	500 VA (5kV/100mA)
Maximum Rated Current	100mA (0.5kV < V ≤ 5kV) 10mA (0.05kV ≤ V ≤ 0.5kV)
Output-Voltage Waveform	Sine wave
Output-Voltage Frequency	50 Hz / 60 Hz selectable
Voltage Regulation	± (1% + 5V) [maximum rated load → no load]
Voltmeter Accuracy	± (1% of reading + 5V)
Current Measurement Range	1μA~100.0mA
Current Best Resolution	1μA / 10μA / 100μA
Current Measurement Accuracy	±(1.5% of reading + 30μA)
Current Offset	60μA Maximum
Window Comparator Method	Yes
ARC Detect	Yes
RAMP UP (Rise Time)	0.1s~999.9s
RAMP DOWN (Fall Time)	0.0s~999.9s

TIMER (Test Time)*	OFF, 0.3s~999.9s	
TIMER Accuracy	±(100ppm + 20ms)	
WAIT TIME	0.0s~999.9s	
GND	ON/OFF	
DC WITHSTANDING		
Output-Voltage Range	0.050kV~6.000kV	
Output-Voltage Resolution	1V	
Output-Voltage Accuracy	± (1% of setting + 5V) [no load]	
Maximum Rated Load	100W (5kV/20mA)	
Maximum Rated Current	20mA (0.5kV < V ≤ 6kV) 2mA (0.05kV ≤ V ≤ 0.5kV)	
Voltage Regulation	± (1% + 5V) [maximum rated load → no load]	
Voltmeter Accuracy	± (1% of reading + 5V)	
Current Measurement Range	1μA~20.00mA	
Current Best Resolution	0.1μA /1μA /10μA	
Current Measurement Accuracy	±(1.5% of reading + 3μA) when I Reading < 1mA ±(1.5% of reading + 30μA) when I Reading ≥ 1mA	
Current Offset	5μA Maximum	
Window Comparator Method	Yes	
ARC Detect	Yes	
RAMP UP (Rise Time)	0.1s~999.9s	
RAMP DOWN (Fall Time)	0.0s~999.9s	
TIMER (Test Time)*	OFF, 0.3s~999.9s	
TIMER Accuracy	±(100ppm + 20ms)	
WAIT TIME	0.0s~999.9s	
GND	ON/OFF	
INSULATION RESISTANCE		
Output Voltage	50V~1200V dc	
Output-Voltage Resolution	50V	
Output-Voltage Accuracy	± (1% of setting + 5V) [no load]	
Resistance Measurement		
Test Voltage	Display Range	Measurement Range / Accuracy
50V≤V≤100V	0.1MΩ~ 10.00GΩ	0.1MΩ~1MΩ : ±(5% of reading + 3 count) 1 MΩ~50MΩ : ±(5% of reading + 1 count)
150V≤V≤450V	0.1MΩ~ 20.00GΩ	51MΩ~2GΩ : ±(10% of reading + 1 count)
500V≤V≤1200V	0.1MΩ~ 50.00GΩ	0.1MΩ~1MΩ : ±(5% of reading + 3 count) 1 MΩ~500MΩ : ±(5% of reading + 1 count) 501MΩ~9.999GΩ : ±(10% of reading + 1 count) 10GΩ~50GΩ : ±(20% of reading + 1 count)*
Voltage Regulation	± (1% + 5V) [maximum rated load → no load]	
Voltmeter Accuracy	± (1% of reading + 5V)	
Short-Circuit Current	10mA max.	
Output Impedance	2kΩ	
Window Comparator Method	Yes	
RAMP UP (Rise Time)	0.1s~999.9s	
RAMP DOWN (Fall Time)	0.0s~999.9s	
TIMER (Test Time)*	OFF, 0.3s~999.9s	
TIMER Accuracy	±(100ppm + 20ms)	
WAIT TIME	0.0s~999.9s	
GND	ON/OFF	
Ground Bond		
Output-Current	03.00A~32.00A ac	
Output-Current Resolution	0.01A	
Output-Current Accuracy	3A≤ I ≤ 8A : ±(1% of reading + 0.2A) 8A<I≤ 32A : ±(1% of reading + 0.05A)	
Test-Voltage	8Vac max (open circuit)	

Test-Voltage Frequency	50Hz/60Hz selectable
Ohmmeter Measurement Range	1mΩ~ 650mΩ
Ohmmeter Measurement Resolution	0.1mΩ
Ohmmeter Measurement Accuracy	±(1% of reading + 2 mΩ)
Window Comparator Method	Yes
TIMER (Test Time)	0.3s~999.9s
TIMER Accuracy	±(100ppm + 20ms)
Test Method	Four Terminal
GND	ON/OFF
Continuity Test	
Output-Current	100mA dc (fixed)
Ohmmeter Measurement Range	0.10Ω~ 70.00Ω
Ohmmeter Measurement Resolution	0.01Ω
Ohmmeter Measurement Accuracy	±(10% of reading + 2 Ω)
Window Comparator Method	Yes
TIMER (Test Time)*	0.3s~999.9s
TIMER Accuracy	±(100ppm + 20ms)
MEMORY	
Single Step Memory	MANU : 100 blocks
Automatic Testing Memory	AUTO : 100 blocks, manu per auto : 10
INTERFACE	
REMOTE (Front) terminal	Standard
USB host (Front)	Standard
Rear Output	Standard
RS-232C	Standard
USB device	Standard
Signal I/O	Standard
GPIB	Option
LAN	Option
DISPLAY	
	7" color LCD
POWER SOURCE	
	AC 100V~240V ± 10%, 50Hz/60Hz
DIMENSION & WEIGHT	
GPT-15001/15002/15003	380(W) x 148(H) x 492(D) mm; Approx. 17kg
GPT-15004	380(W) x 148(H) x 546(D) mm; Approx. 21kg

* When Ground Mode is "ON", the measurement range is 30GΩ max. and adding 10% error for accuracy.