## AZ9403

# 10 AMP MINIATURE POWER RELAY

#### **FEATURES**

- · Class F Insulation Standard
- 10 Amp switching capability
- 4 kV dielectric strength
- Epoxy sealed version available
- UL, CUR file E44211
- VDE certificate 40049971



#### **CONTACTS**

Arrangement	SPST (1 Form A) SPDT (1 Form C)
Ratings	Resistive load:  Max. switched power: 150 W or 2770 VA  Max. switched current: 10 A (N.O.), 3 A (N.C.)  Max. switched voltage: 150 VDC* or 400 VAC  * Note: If switching voltage is greater than 30 VDC, special precautions must be taken.  Please contact the factory.
Rated Load UL VDE	Normally open contact (N.O.)  10 A at 125 VAC, General Use, 80k cycles 70°C  10 A at 120 VAC, resistive, 80k cycles 70°C  5 A at 277 VAC, General Use, 100k cycles 70°C  5 A at 30 VDC, resistive, 100k cycles 70°C  4 A at 120 VAC, resistive, 100k cycles 105°C  1 A at 120 VAC, tungsten, 6k cycles 105°C  2.5 FLA / 15 LRA at 120 VAC, 6k cycles 105°C  Normally closed contact (N.C.)  3 A at 277 VAC general use, 100k cycles 70°C  Normally open contact (N.O.)  5A (cos\phi1), 277VAC 100k cycles 70°C  Normally closed contact (N.O.)  5A (cos\phi1), 277VAC 50k cycles 70°C sensitive Coil  Normally closed contact (N.C.)  3A (cos\phi1), 277 VAC general use, 100k cycles 70°C
Material	silver tin oxide
Resistance	< 100 milliohms initially (at 6 V, 1 A, voltage drop method)

#### **GENERAL DATA**

Life Expectancy Mechanical Electrical	Minimum operations $1 \times 10^7$ $1 \times 10^5$ at 10 A 277 VAC Res.		
Operate Time (max.)	8 ms at nominal coil voltage		
Release Time (max.)	5 ms at nominal coil voltage (with no coil suppression)		
Dielectric Strength (at sea level for 1 min.)	4000 Vrms coil to contact 1000 Vrms between open contacts		
Insulation Resistance	1 x 10 <sup>9</sup> ohms minimum at 500 VDC		
Dropout	Greater than 5% of nominal coil voltage		
Ambient Temperature Operating Storage	At nominal coil voltage -40°C (-40°F) to 90°C (194°F) Class B -40°C (-40°F) to 110°C (230°F) Class F -40°C (-40°F) to 130°C (266°F) Class B -40°C (-40°F) to 155°C (311°F) Class F		
Vibration	0.062" (1.5 mm) DA at 10-55 Hz		
Shock Functional Destructive	98m/s <sup>2</sup> 980m/s <sup>2</sup>		
Enclosure	P.B.T. polyester		
Terminals	Tinned copper alloy, P.C.		
Max. Solder Temp.	270°C (518°F)		
Max. Solder Time	5 seconds		
Max. Solvent Temp.	80°C (176°F)		
Max. Immersion Time	30 seconds		
Weight	7 grams		
Packing unit in pcs	100 per styrofoam tray / 1000 per cartonbox		

#### COIL

Power At Pickup Voltage (typical)	409mW (standard coil) 181mW (sensitive coil)
Max. Continuous Dissipation	845mW at 20°C (68°F) ambient (standard) 500mW at 20°C (68°F) ambient (sensitive)
Temperature Rise	40°C (72°F) at nominal coil voltage (standard coil) 20°C (36°F) at nominal coil voltage (sensitive coil)
Temperature	Max. 155°C (311°F) Class F

#### **NOTES**

- 1. All values at 20°C (68°F).
- 2. Relay may pull in with less than "Must Operate" value.
- 3. Specifications subject to change without notice.

AMERICAN ZETTLER, INC.



#### **RELAY ORDERING DATA**


STANDARD COIL	TANDARD COIL							
	COIL SPE	CIFICATIONS		ORDER NUMBER*				
Nominal Coil VDC	Must Operate VDC	Max. Continuous VDC	Coil Resistance Ohm ± 10	Form A (SPST)	Form C (SPDT)			
3	2.3	3.9	20	AZ9403-1A-3D	AZ9403-1C-3D			
5	3.8	6.5	55	AZ9403-1A-5D	AZ9403-1C-5D			
6	4.5	7.8	80	AZ9403-1A-6D	AZ9403-1C-6D			
9	6.8	11.7	180	AZ9403-1A-9D	AZ9403-1C-9D			
12	9.0	15.6	320	AZ9403-1A-12D	AZ9403-1C-12D			
18	13.5	23.4	720	AZ9403-1A-18D	AZ9403-1C-18D			
24	18.0	31.2	1,280	AZ9403-1A-24D	AZ9403-1C-24D			
48	36.0	62.4	5,120	AZ9403-1A-48D	AZ9403-1C-48D			

<sup>\*</sup> Add suffix "E" at the end of order number for sealed version. VDE Rating for 5, 9, 12, 12 VDC coil only.

ENSITIVE COIL								
	COIL SPE	ORDER NUMBER*						
Nominal Coil VDC	Must Operate VDC	Max. Continuous VDC	Coil Resistance Ohm ± 10%	Form A (SPST)				
3	2.3	4.5	45	AZ9403-1A-3DS				
5	3.8	7.5	125	AZ9403-1A-5DS				
6	4.5	9.1	180	AZ9403-1A-6DS				
9	6.8	13.5	400	AZ9403-1A-9DS				
12	9.0	18.0	720	AZ9403-1A-12DS				
18	13.5	27.0	1,600	AZ9403-1A-18DS				
24	18.0	36.0	2,800	AZ9403-1A-24DS				

<sup>\*</sup> Add suffix "E" at the end of order number for sealed version. VDE Rating for 5, 9, 12, 12 VDC coil only.

#### **MECHANICAL DATA**



Dimensions in inches with metric equivalents in parentheses. Tolerance: ± .010"

### 1ERICAN ZETTLER, INC.

02/28/19