WWW.PHIHONG.COM



10W USB Interchangeable Plug* Adapter



*Plugs sold separately

Features	
USB Socket	Low Leakage Current
• Field Changeable AC Plugs	DOE Level VI Compliance
• <75mW Power Consumption with no	• EU COC V5 Tier 2 Compliance
load at 230VAC 50Hz	Voltage Drop Compensation
Applications	
Personal Electronics	Portable Equipment
Peripherals	Networking
Safety Approvals	
• cUL/UL60950-1	• cUL/UL62368-1
• IEC60950-1	• IEC62368-1
• RCM AS/NZS 60950-1	• CE
• KC/KCC	• EAC
• PSE	
Mechanical Characteristics	
• Length: 75.75mm (2.98in)	• Height: 33.08mm (1.30in)
• Width: 45.5mm (1.79in)	• Weight: 52g (1.83oz)

Output Specifications	

Madal	DC Output	Load		Ripple¹	Regulation
Model	Voltage	Min.	Max.	P-P (max.)	Line & Load
PSAF10R-050QA-R	5V	0A	2A	150mV	±5%

Notes:

Measuring is done by 20MHz bandwidth oscilloscope and terminated each output with a 1uF low ESR aluminum electrolytic capacitor and a 0.1uF ceramic capacitor in parallel 1.

Phihong is not responsible for any error and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information. Revised 1/16/2020

PSAF10R-050QA-R Characteristics¹

INPUT: AC Input Voltage Rating 100 to 240V AC

AC Input Voltage Range 90 to 264V AC

AC Input Frequency 47 to 63Hz

Input Current 0.28A (RMS) max for 115Vac/60Hz 0.16A (RMS) max for 230Vac/50Hz

Leakage Current 20uA Max @254Vac/50Hz

Inrush Current 60A max at 230VAC/50Hz (Cold start at ambient 25°C)

OUTPUT: Output Power 10W

Efficiency² DOE Level VI and CoC V5 tier 2

ENVIRONMENTAL:

TemperatureOperation0 to +40°CNon-operation-20 to +70°CRelative Humidity90% RH Max

Emissions

Complies with FCC Class B Complies with EN55032 Class B

WWW.PHIHONG.COM

Immunity

ESD: EN 61000-4-2 Air ± 15 KV Contact ± 8 KV Surge: EN 61000-4-5 Line to Line 1KV Line or Neutral to PE 2KV RS : EN61000-4-3. 3V/m EFT : EN61000-4-4. 1KV Voltage Dips : EN61000-4-11, Level 3

Over-Voltage Protection Output voltage shall not exceed 8V

Over-Current Protection 3A Max

Short-Circuit Protection Auto recovery and no component damage

Dielectric Withstand (Hi-pot) Test Pri. to Sec. 3000VAC 10mA for 1 Minute

DC Output Connector USB Type A

AC Input Clips (sold separately)

RPA – US RPB – Brazil RPC – China RPE – Europe RPH – Korea RPI – India RPK – UK RPN – Argentina RPS – Australia RPX – IEC320 C8


Notes:


1. The characteristics defined are at ambient temperature of 25°C unless otherwise specified


2. Efficiency is measured after 30 minutes burn-in


Dimension Diagram Unit: mm

WWW.PHIHONG.COM









Supplier's Declaration of Conformity 47 CFR § 2.1077 Compliance Information

PSAF10R-050QA-R

Phihong USA Corporation 47800 Fremont Boulevard Fremont, CA 94538 Telephone: (510) 445-0100 www.phihong.com

NOTE: This model has/The models in this products series have been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- -Reorient or relocate the receiving antenna.
- —Increase the separation between the equipment and receiver.
- -Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- -Consult the dealer or an experienced radio/TV technician for help.

Changes or modifications to equipment not expressly approved by PHIHONG could void the user's authority to operate the equipment.