

## **NEMA8 STEPPER MOTOR**

NEMA08-01



Our NEMA 8 series are very small high torque stepper motors that can reach speeds of up to 3000 rpm.

These motors are used in model making and maker scene as well as in the industrial environment (e.g. positioning of optics, dosing pumps, interlocks, etc.).

MAIN FEATURES	
Shaft	Ø 4 x 18,5 mm
Connection	6 pin JST socket
Dimensions	20 x 22 x 30 mm
Items delivered	NEMA8 stepper, connection cable


PERFORMANCE SPECIFICATIONS	
Holding torque	16 mNm
Rated Voltage	3.9 V
Rated Current	0.6 A
Step Angle	1.8°±5%
No. of Phases	2
Phase Resistance	6.5 Ω
Phase inductivity	1.7 mH
Isolation resistance	100 MΩ min. @500V
Isolation class	B (130 °C)
Rotational inertia	2 g·cm²
Detent Torque	18 mNm
Operating temperature	-10 °C - 50 °C


FURTHER DETAILS	
Article No.	NEMA08-01
EAN:	4250236821665
Customs Tariff No.	8501109990

Published: 23.07.2021

## <u>joy-it</u>

## **DRAWING**





## WIRING

