

NEMA8 STEPPER MOTOR

NEMA08-03



Our NEMA 8 series are very small high torque stepper motors that can reach speeds of up to 3000 rpm.

These motors are used in model making and maker scene as well as in the industrial environment (e.g. positioning of optics, dosing pumps, interlocks, etc.).


MAIN FEATURES	
Shaft	Ø 4 x 8.5 mm
Interface connection	6 pin JST socket
Dimensions	20 x 22 x 27.3 mm
Items delivered	NEMA8 stepper, connection cable


PERFORMANCE SPECIFICATIONS	
Holding torque	22 mNm
Rated Voltage	4.26 V
Rated Current	0.6 A
Step Angle	1.8°±5%
No. of Phases	2
Phase Resistance	7.1 Ω
Phase inductivity	2.1 mH
Isolation resistance	100 MΩ min. @500 V DC
Isolation class	B (130 °C)
Rotational inertia	2 g·cm²
Detent Torque	3 mNm
Operating temperature	-10 °C - 50 °C

FURTHER DETAILS	
Article No.	NEMA08-03
EAN:	4250236821689
Customs Tariff No.	8501109990

<u>joy-it</u>

DRAWING





WIRING

