


6.5 Alarm Types



7. Specifications

Device Type : Temperature Controller
Housing & Mounting : 76mm x 34.5mm x 71mm plastic housing for panel Mounting. Panel cut-out is 71x29mm.
Protection Class : NEMA 4X (Ip65 at front, Ip20 at rear).
Weight : Approximately 0.20 Kg.
Environmental Ratings : Standard, indoor at an altitude of less than 2000 meters with none condensing humidity.
Storage / Operating Temperature : -30 °C to +80 °C / -20 °C to +70 °C
Storage / Operating Humidity : 90 % max. (None condensing)
Installation : Fixed installation
Overvoltage Category : II.
Pollution Degree : II, office or workplace, none conductive pollution
Operating Conditions : Continuous
Supply Voltage and Power : 230V~ (±%15) 50/60Hz - 1.5VA
 : 115V~ (±%15) 50/60Hz - 1.5VA
 : 24V~ (±%15) 50/60Hz - 1.5VA
 : 24V~ (±%15) 50/60Hz - 1.5VA
 : 10 - 30V--- 1.5W
Temperature Sensor Input : NTC, PTC, TC, RTD
NTC input type : NTC (10 kΩ @25 °C)
PTC input type : PTC (1000 Ω @25 °C)
Thermocouple input type : J, K (IEC584.1) (ITS 90)
Thermoresistance input type : PT-100, PT-1000 (IEC751) (ITS 90)
Accuracy : ± 1 % of full scale for thermoresistance
Cold Junction Compensation : Automatically ± 0.1°C / ± 1°C
Sensor Break Protection : Upscale
Sampling Cycle : 3 samples per second
Control Form : PID or ON / OFF
Relay Output : 16(8) A@250 V~ for Resistive load (Compressor Output) (Electrical life : 100.000 switching at full load)
 : 5 A@250 V~ for Resistive load (Alarm Output)
Optional SSR Drive Output : Maximum 20mA, Maximum 15V---
Display : 14 mm Red 4 digits LED Display
LED : S (Green), P (Green), °C (Yellow), °F (Yellow), Compressor Output (Red), Heating Output (Red)
Internal Buzzer : >83dB
Approvals : EAC, CE

13

14

8. Ordering Information

ESM-3720 (77x35 DIN Sizes)	A	B	C	D	E	FG	HI	U	V	W	Z
	0	/	01	00	/	1	0	0			
A Supply Voltage											
2	24V~ (±%15) 50/60Hz - 1.5VA										
3	24V~ (±%15) 50/60Hz - 1.5VA										
4	115V~ (±%15) 50/60Hz - 1.5VA										
5	230V~ (±%15) 50/60Hz - 1.5VA										
8	10 - 30 V ---										
BC Input Type	Scale(°C)										
05	J, Fe CuNi IEC584.1(ITS90)										0°C/32°F ; 800°C/1472°F
10	K, NiCr Ni IEC584.1(ITS90)										0°C/32°F ; 999°C/1830°F
11	PT 100, IEC751(ITS90)										-50°C/-58°F ; 400°C/752°F
09	PT 100, IEC751(ITS90)										-19.9°C/-4°F ; 99.9°C/212°F
14	PT 1000, IEC751(ITS90)										-50°C/-58°F ; 400°C/752°F
13	PT 1000, IEC751(ITS90)										-19.9°C/-4°F ; 99.9°C/212°F
12	PTC (Not-1)										-50°C/-58°F ; 150°C/302°F
18	NTC (Not-1)										-50°C/-58°F ; 100°C/212°F
E Control Output											
1	Relay Output (16(8) A@250 V~, at resistive Load, 1 NO)										
2	SSR Driver Output (Maximum 20m, Maximum 17V---)										
FG Alarm Output											
01	Relay Output (5 A@250 V~, at resistive Load, 1 NO)										
V Temp. Sensor which is given with ESM-3720											
0	None										
1	PTC-M6L40.K1.5 (PTC Air Probe 1.5 mt Silicon Cable)										
2	PTCS-M6L30.K1.5.1/8" (PTC Liquid Probe 1.5 mt Silicon Cable)										
3	NTC-M5L20.K1.5 (NTC Sensor, thermoplastic moulded with 1.5 m cable for cooling application)										
4	NTC-M6L50.K1.5 (NTC Sensor, stainless steel housing with 1.5 m cable for cooling application)										
9	Customer										

All order information of ESM-3720 Temperature Controller are given on the table at above. User may form appropriate device configuration from information and codes that at the table and convert it to the ordering codes. Firstly, supply voltage then other specifications must be determined. Please fill the order code blanks according to your needs.

Please contact us, if your needs are out of the standards.

Note-1: If input type is selected PTC or NTC (BC= 12, 18), Temperature sensor is given with the device. For this reason, if input type is selected as PTC, sensor type (V = 0, 1 or 2) or if input type is selected as NTC, sensor type (V = 0, 3 or 4) must be declared in ordering information.

15

9. Optional Accessories

1. RS-485 Module



RS-485 Communication Interface

2. PROKEY Programming Module



The device is programmed (Upload or Download) by using the parameters.

! ~ Vac,
 --- Vdc
 ~ Vdc or Vac can be applied

EMKO Thank you very much for your preference to use Emko Elektronik products, please visit our Your Technology Partner web page to download detailed user manual. www.emkoelektronik.com.tr

16

EMKO

ESM-3720 77x35 DIN Size Temperature Controller



ESM-3720 77 x 35 DIN Size Digital Temperature Controller

- 4 Digits Display
- NTC Input or PTC Input or J Type thermocouple Input or, K Type thermocouple Input or, 2-Wire PT-100 Input or, 2-Wire PT-1000 Input (Must be determined in order.)
- Adjustable temperature offset
- PID or ON/OFF temperature control
- Selectable heating or cooling function
- Selection of operation with hysteresis
- Adjustable temperature offset
- Set value low limit and set value high limit boundaries
- Operation selection of compressor operates continuously, stops or operates periodically in case of sensor defect
- Compressor protection delays
- Alarm parameters
- Adjustable internal buzzer according to sensor defect status.
- Password protection for programming section
- Installing parameters using Prokey
- Remote access, data collecting and controlling with Modbus RTU
- Having CE mark according to European Norms

Instruction Manual. ENG ESM-3720 01 V05 03/18

1.3 Installation

A visual inspection of this product for possible damage occurred during shipment is recommended before installation. It is your responsibility to ensure that qualified mechanical and electrical technicians install this product.

If there is danger of serious accident resulting from a failure or defect in this unit, power off the system and separate the electrical connection of the device from the system.

The unit is normally supplied without a power supply switch or a fuse. Use power switch and fuse as required.

Be sure to use the rated power supply voltage to protect the unit against damage and to prevent failure.

Keep the power off until all of the wiring is completed so that electric shock and trouble with the unit can be prevented.

Never attempt to disassemble, modify or repair this unit. Tampering with the unit may result in malfunction, electric shock or fire.

Do not use the unit in combustible or explosive gaseous atmospheres.

During putting equipment in hole on the metal panel while mechanical installation some metal burrs can cause injury on hands, you must be careful.

Montage of the product on a system must be done with its fixing clamps. Do not do the montage of the device with inappropriate fixing clamp. Be sure that device will not fall while doing the montage.

It is your responsibility if this equipment is used in a manner not specified in this instruction manual.

1.4 Warranty

EMKO Elektronik warrants that the equipment delivered is free from defects in material and workmanship. This warranty is provided for a period of two years. The warranty period starts from the delivery date. This warranty is in force if duty and responsibilities which are determined in warranty document and instruction manual performs by the customer completely.

1.5 Maintenance

Repairs should only be performed by trained and specialized personnel. Cut power to the device before accessing internal parts. Do not clean the case with hydrocarbon-based solvents (Petrol, Trichlorethylene etc.). Use of these solvents can reduce the mechanical reliability of the device. Use a cloth dampened in ethyl alcohol or water to clean the external plastic case.

1.6 Manufacturer Company

Manufacturer Information:
 Emko Elektronik Sanayi ve Ticaret A.Ş.
 Demirtaş Organize Sanayi Bölgesi Karanfil Sk. No:6 16369 BURSA/TURKEY
 Phone : +90 224 261 1900
 Fax : +90 224 261 1912
Repair and maintenance service information:
 Emko Elektronik Sanayi ve Ticaret A.Ş.
 Demirtaş Organize Sanayi Bölgesi Karanfil Sk. No:6 16369 BURSA/TURKEY
 Phone : +90 224 261 1900
 Fax : +90 224 261 1912

3

1. Preface


ESM-3720 series temperature controllers are designed for measuring and controlling temperature. They can be used in many applications with their On / Off control form, heating and cooling control form and easy-use properties. Some application fields which they are used are below:

Application Fields	Applications
Glass	Heating
Food	Baking Ovens
Plastic	Incubators
Petro-Chemistry	Storages
Textile,	Automotive Air Conditioning
Machine Production Industries Etc...	Etc...

1.1 Environmental Ratings


- Operating Temperature : -20 to 70 °C
- Max. Operating Humidity : 90% Rh (non-condensing)
- Altitude : Up to 2000 m.
- Forbidden Conditions:
 Corrosive atmosphere
 Explosive atmosphere
 Home applications (The unit is only for industrial applications)

1.2 General Specifications




2


2. General Description



2.1 Front View and Dimensions of ESM-3720 Temperature Controller




2.2 Panel Cut-Out



4


2.3 Panel Mounting



1-Before mounting the device in your panel, make sure that the cut-outs of the right size.
3-Insert the mounting clamps to the fixing sockets that located left and right sides of device and make the unit completely immobile within the panel

2-Insert the device through the cut-out. If the mounting clamps are on the unit, put out them before inserting the unit to the panel.

2.4 Removing from the Panel



1-Pull mounting clamps from left and right fixing sockets.
2-Pull the unit through the front side of the panel

Before starting to remove the unit from panel, power off the unit and the related system.

3. Using Prokey

TO USE PROKEY, VALUE OF THE Prc PARAMETER MUST BE '0'. IF Prc=1 AND SET BUTTON IS PRESSED, [Prc] MESSAGE WILL BE SHOWN. 10s. LATER DEVICE TURNS BACK TO THE MAIN OPERATION SCREEN OR YOU CAN PRESS SET BUTTON TO TURN BACK TO MAIN OPERATION SCREEN.

DOWNLOADING FROM DEVICE TO PROKEY

1.The device is programmed by using the parameters.
2.Energize the device then put in PROKEY and press SET button. [Prc] Message is shown on the display. When the loading has finished, [End] message is shown.
3.Press any button to turn back to main operation screen.
4.Remove the PROKEY.


NOTE: [Prc] message is shown when an error occurs while programming. If you want to reload, put in PROKEY and press SET button. If you want to quit, remove PROKEY and press SET button. The device will turn back to main operation screen.

DOWNLOADING FROM PROKEY TO DEVICE

1.Switch off the device.
2.Put in PROKEY then energize the device.
3.When the device is energized, the parameter values in PROKEY, start downloading to the device automatically. At first, [Prc] message is shown on the display, when loading has finished, [End] message is shown.
4.After 10 seconds device starts to operate with new parameter values.
5.Remove the PROKEY.

NOTE: [Prc] message is shown when an error occurs while programming. If you want to reload, switch off the device and put in PROKEY then energize the device. If you want to quit remove PROKEY and press SET button. The device will turn back to main operation screen.

5.Front Panel Definition and Accessing to the Menus




BUTTON DEFINITIONS

- Increment Button :**
 - ** It is used to increase the value in the Set screen and Programming mode.
- Decrement, Silencing Buzzer and Downloading to Prokey Button :**
 - ** It is used to decrease the value in the Set screen and Programming mode.
 - ** It is used to silence the buzzer.
 - ** If Prc = 0, it is used to download from device to prokey.
- Set Button :**
 - ** In the main operation screen; if this button pressed, temperature set value will be displayed. Value can be changed using increment and decrement buttons. When Enter button pressed, value is saved and alarm set value is displayed. Value can be changed using increment and decrement buttons. When Enter button pressed, alarm set value is saved and returns back to main operation screen.
 - ** To access the programming screen; in the main operation screen, press this button for 5 seconds.
- Enter Button :**
 - ** It is used to saving value in the Set screen and programming screen.
 - **In the main operation screen; press ENTER button for 3 seconds to start Auto Tune operation..

LED DEFINITIONS

- Cooling led :**
 - ** This led indicates that cooling control is selected and process output relay is active. If any of compressor protection time active, this led blinks.
- Heating led :**
 - ** This led indicates that heating control is selected and process output relay is active.
- Alarm led :**
 - ** This led indicates that alarm output relay is active.
- Celcius led :**
 - ** Indicates that device is in °C mode.
- Fahrenheit led :**
 - ** Indicates that device is in °F mode.
- Auto Tune / Self Tune led :**
 - ** Indicates that device is operating Auto Tune or Self Tune.
- Set led :**
 - ** Indicates that device is in Set value changing mode.
- Program led :**
 - **Blinks in programming mode .


6. Changing and Saving Temperature Set Value And alarm Set Value



When SET button pressed "S" led will be active and temperature set value will be displayed.


Temperature set value can be changed with increment and decrement buttons.

4. Electrical Wiring Diagram




4.1 Supply Voltage Input Connection of the Device

Power Supply Connection Make sure that the power supply voltage is the same indicated on the instrument. Switch on the power supply only after that all the electrical connections have been completed. Supply voltage range must be determined in order. While installing the unit, supply voltage range must be controlled and appropriate supply voltage must be applied to the unit.



Note-1 : External fuse is recommended.


4.2 Device Label and Connection Diagram



- P** PID - Proportional Control Parameter (Default = 10.0) MODBUS ADRES:40007 This parameter can be adjusted from %1.0 to %100.0
- I** PID-Integral Parameter(Default = 100) MODBUS ADRES:40008 This parameter value can be adjusted from 0 to 3600.
- d** PID-Derivativel Parameter (Default = 25.0) MODBUS ADRES:40009 This parameter value can be adjusted from 0.0 to 999.9
- t** PID-Period parameter(Default = 10) MODBUS ADRES:40010 This parameter value can be adjusted from 0 to 150 second.
- PuL** Operation Scale Minimum Parameter (Default = Minimum Value of Device Scale) MODBUS ADDRESS:40011 This parameter value can be adjusted from minimum value of device scale to operation scale maximum parameter[PuH]
- PuH** Operation Scale Maximum Parameter (Default = Maximum Value of Device Scale) MODBUS ADDRESS:40012 This parameter value can be adjusted from operation scale minimum parameter[PuL] to maximum value of the device scale.
- HSt** Hysteresis Parameter for Compressor Output (Default = 3) MODBUS ADDRESS:40013 from 1 to 20°C for NTC (-50°C, 100°C) or PTC (-50°C, 130°C) or J Type TC (0°C, 800°C) or K Type TC (0°C, 1000°C) or PT-100 Type (-50°C, 400°C) or PT-1000 Type (-50°C, 400°C) or PT-100 Type (-20°C, 100°C), from 1 to 36°F for NTC (-58°F, 212°F) or PTC (-58°F, 266°F) or J Type TC (32°F, 1472°F) or K Type TC (32°F, 1830°F) or PT-100 Type (-58°F, 752°F) or PT-1000 Type (-58°F, 752°F) or PT-100 Type (-4°F, 212°F) from 0.1 to 10.0°C for NTC(-50.0°C, 100.0°C) or PTC (-50.0°C, 130.0°C) or PT-100 (-19.9°C, 99.9°C), from 0.1 to 18.0°F for NTC(-58.0°F, 212.0°F) or PTC (-58.0°F, 266.0°F) or PT-100 (-4.0°F, 212.0°F), In ON/OFF control algorithm, temperature value is tried to keep equal to set value by opening or closing the last control element. ON/OFF controlled system, temperature value oscillates continuously. Temperature value's oscillation period or amplitude around set value changes according to controlled system. For reducing oscillation period of temperature value, a threshold zone is formed below or around set value and this zone is named hysteresis.
- SuL** Minimum Temperature Set Value Parameter (Default = Minimum Value of Device Scale) MODBUS ADDRESS:40014 Temperature set value can not be lower than this value. This parameter value can be adjusted from operation scale minimum parameter[PuL] to maximum temperature set value parameter[SuH]
- SuH** Maximum Temperature Set Value Parameter (Default = Maximum Value of Device Scale) MODBUS ADDRESS:40015 Temperature set value can not be bigger than this value. This parameter value can be adjusted from minimum temperature set value parameter[SuL] to operation scale maximum parameter[PuH]
- oFt** Sensor Offset Parameter (Default = 0) MODBUS ADDRESS:40016 from -20 to 20 °C for NTC(-50°C, 100°C) or PTC(-50°C, 130°C) or J Type TC (0°C, 800°C) or K Type TC (0°C, 1000°C) or PT-100(-50°C, 400°C) or PT-1000 (-50°C, 150°C) or PT-100 (-20°C, 100°C), from -36 to 36 °F for NTC(-58°F, 212°F) or PTC(-58°F, 266°F) or J Type TC (32°F, 1472°F) or K Type TC (32°F, 1830°F) or PT-100(-58°F, 752°F) or PT-1000(-58°F, 752°F) or PT-100(-4°F, 212°F), from -10.0 to 10.0°C for NTC(-50.0°C, 100.0°C) or PTC (-50.0°C, 130.0°C) or PT-100 (-19.9°C, 99.9°C), from -18.0 to 18.0°F for NTC(-58.0°F, 212.0°F) or PTC (-58.0°F, 266.0°F) or PT-100 (-4.0°F, 212.0°F).

- Pos** Compressor Start Delay at Power On Parameter (Default = 0) MODBUS ADDRESS:40017 When power is first applied to the device, compressor is on when this time delay is expired. It can be adjusted from 0 to 20 minutes.
 - SPd** Compressor Stop-Start Delay Parameter (Default = 0) MODBUS ADRES:40018 When compressor is inactive, this time delay must be expired for activation of the compressor. It can be adjusted from 0 to 20 minutes.
 - Std** Compressor Start-Start Delay Parameter (Default = 0) MODBUS ADRES:40019 This time delay must be expired between two activation of the compressor. It can be adjusted from 0 to 20 minutes.
 - PdF** Sensor Defect Parameter (Default = 0) MODBUS ADRES:40020
 - 0 Compressor is OFF in case of sensor defect.
 - 1 Compressor is ON in case of sensor defect.
 - 2 Compressor operates periodically according to [Pon] and [Pof] Time periods in case of sensor defect.
 - Pon** Compressor is active during this time period in case of probe defect (Default = 0) MODBUS ADRES:40021 If probe defect parameter [PdF] is 2, then this parameter is observed. It can be adjusted from 0 to 99 minutes.
 - Pof** Compressor is inactive during this time period in case of probe defect (Default = 0) MODBUS ADRES:40022 If probe defect parameter [PdF] is 2, then this parameter is observed. It can be adjusted from 0 to 99 minutes.
 - ALS** Temperature Alarm Function Selection Parameter (Default = 1) MODBUS ADDRESS:40023
 - 0 Alarm function is inactive.
 - 1 Process High alarm selected.
 - 2 Process Low alarm selected.
 - 3 Deviation High alarm selected.
 - 4 Deviation Low alarm selected.
 - 5 Deviation Band alarm selected.
 - 6 Deviation Range alarm selected.
 - 7 Deviation Range High alarm selected.
- Note: If this parameter is select 0, [StL], [ALH], [SuL], [SuH], [Pon], [Pof] and [PdF] parameters will be not observed
- ASt** Temperature Alarm Set Parameter (Default = 80) MODBUS ADDRESS:40024 This parameter value can be programmed between temperature minimum alarm set [SuL] parameter and temperature alarm set maximum [SuH] parameter.
 - ALH** Temperature Alarm Hysteresis Parameter (Default = 3) MODBUS ADDRESS:40025 This parameter value can be adjusted from 0.1 to %50 of the device scale if Pnt parameter is 1, 1 to %50 of the device scale if Pnt parameter is 0.
 - RuL** Temperature Minimum Alarm Parameter (Default = Minimum Value of Device Scale) MODBUS ADDRESS:40026 If temperature alarm is active, this parameter value can be adjusted from operation scale minimum parameter [PuL] to temperature alarm set maximum parameter value [SuH].
 - RuH** Temperature Alarm Maximum Parameter (Default = Maximum Value of Device Scale) MODBUS ADDRESS:40027 If temperature alarm is active, this parameter value can be adjusted from temperature alarm set value parameter [RuL] to operation scale maximum parameter [PuH].
 - Ron** Temperature Alarm On Delay Time Parameter (Default = 0) MODBUS ADDRESS:40028 Temperature alarm on delay time can be defined with this parameter. It can be adjusted from 0 to 99 minutes.

6.4 Entering To The Programming Mode, Changing and Saving Parameter



When SET button is pressed for 5 seconds, "P" led starts to blink. If programming mode entering password is 0, [Prc] Temperature Unit screen is observed instead of programming screen [Prc] will be observed.

Note1: If programming mode accessing password is 0, [Prc] Temperature Unit screen is observed instead of programming screen [Prc] will be observed.

Programming Mode Entering Screen Press OK button for accessing to the password entering screen.

Password Entering Screen Enter programming mode accessing password with increment and decrement buttons.

Password Entering Screen Press OK button for entering the password.

Note2: If programming mode accessing password is 0, only three parameters are accessible, and the parameter values can be changed.

Programming Screen Press SET button for accessing to the parameter value. Press increment button for accessing to the next parameter, press decrement button for accessing to the previous parameter.

Hysteresis Value for Compressor Output Change the value with increment and decrement buttons.

Hysteresis Value for Compressor Output Press OK button for saving the parameter.

Hysteresis Parameter for Compressor Press increment button for accessing to the next parameter, press decrement button for accessing to the previous parameter

If no operation is performed in programming mode for 20 seconds, device turns to main operation screen automatically.