

Supplier	Article description			Art. No. / GTIN	Warranty
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	DrainPress 3200/24 Set			30181	24 Months
	Master Box Information				
	Master Box dimensions in cm			weight (kg) gross	pack. Unit (pcs.)
	Width	Depth	Height		
-	-	-	-	-	
Artikel Informationen					
Color Box dimensions in cm			weight (kg) net / gross	Qty.	
Width	Depth	Height			
32,0	28,0	47,0	7,0 / 8,4	1	

DrainPress 3200/24 Set

quantity / pallet:

quantity / truck:

Description:

The DrainPress 3200/24 Set is a multi-stage submersible pressure pump for special applications. Ideal for irrigation and drainage with clear or slightly contaminated water. Also suitable for pumping out swimming pools, cisterns or containers. Due to the flat suction up to 1 mm (wipe-dry) excellent for draining rooms. The operation of a sprinkler or a watering shower is also possible. Due to the extensive accessories a flexible and mobile use is possible.

Technical Data:

Nominal performance: 400 Watt
 Delivery height / pressure: 24 m / 2.4 bar max.
 Flow rate max.: 53 l/min / 3200 l/h
 Pump housing: Plastic shockresistant
 Suction level min.: 1 mm
 Grain size max.: 2 mm
 Submersion depth max.: 7 m
 Power cord: 10 m / H05RN-F
 Max. fluid temp.: 35 °C
 Pressure port: 26.44 mm (¾", male)
 Sprinklers max.: 1

Accessories:

10 m hose, sprinkler, rain barrel set, connectors, water gun

Approval marks:



08.12.2020

