SUNON

SPECIFICATION FOR APPROVAL

CUSTOMER :

DESCRIPTION : AXIAL AC FAN

DIMENSIONS : 176X176X89 mm

MODEL : A2179-HBT

P/N : TC.GN

SUNON SPEC. NO. : A17000790G-00

CUSTOMER :

APPROVAL NO.

APPROVED BY

CUSTOMER

(AUTHORIZED)

DRAWN						SPEC.NO	A17000790G-00
	A		Kiddy			ISSUE DATE	05.30.2005
	Anna 09/15	CHECKED	,	APPROVED	Jacky	EDITION	1
	09/10		March			REVISION DATE	09.15.2010
						E.SPEC	EA17110

建準電機工業股份有限公司

SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.


NO. 30, LN. 296, XINYA RD., QIANZHEN DIST., TEL:886-7-8135888

KAOHSIUNG CITY 80673, TAIWAN (R.O.C) FAX:886-7-8230505/8230606/8231010

URL: http://www.sunon.com

E-mail: sunon@email.sunon@onitwich

2010.09.23



AXIAL AC FAN

MODEL: A2179-HBT

P/N : TC.GN

CHARACTERISTICS

1. Motor Design : Reliable Alveolate Motor Construction.

2. Insulation Resistance : 500 Megohms minimum at 500 VDC.

3. Dielectric Strength : 1800 VAC for one second.

4. Motor Protection : Thermal protected.

5. Noise Level : Measured in a semi-anechoic chamber

with background noise level below 15

dB(A). The fan is running in free air with the

microphone at a distance of one meter

from the fan intake.

6. Tolerance : ±15% on rated power and current.

7. Air Performance : Measured by a double chamber. The values

are recorded when the fan speed has stabilized

at rated voltage.

建準電機工業股份有限公司	SPEC.NO	A17000790G-00	REVISION I	DATE 199. 15. 2010
SUNONWEALTH ELECTRIC	ISSUE DATE	05. 30. 2005	EDITIC	1 张 部引
MACHINE INDUSTRY CO., LTD.	PAGE	3 OF 11		2010 00 22

SPECIFICATIONS

MODEL: A2179-HBT

P/N: TC.GN

1-1. Rated Voltage : 220-240 VAC 50/60 Hz

1-2. Operating Voltage Range : 150-250 VAC

1-3. Starting Voltage : 150 VAC (25 deg. C POWER ON/OFF)

1-4. Rated Speed : $2800/3250 \text{ RPM} \pm 10\%$

1-5. Air Delivery : 315/335 CFM

1-6. Static Pressure : 0.65/0.80 Inch-H₂O

1-7. Rated Current : 0.11/0.15 AMP

1-8. Rated Power : 23/30 WATTS

1-9. Noise Level : 62/66 dB(A)

1-10. Direction of Rotation : Clockwise viewed from front of fan blade

1-11. Operating Temperature : -10 to +70 deg. C

1-12. Storage Temperature : -40 to +70 deg. C

1-13. Bearing System : Precision ball bearing system

1-14. Weight : 1960 g

1-15. Safety : UL/CUR/TUV/CE Approvals

1-16. Vibration : Vibration of acceleration 1.5G and

frequency 5~50~5Hz is applied in all

3 directions(X,Y,Z), in cycles of 1 minute each,

for a total vibration time of 30 minutes.

建準電機工業股份有限公司	SPEC.NO	A17000790G-00	REV	ISION	DA	18	09. 15	2019
SUNONWEALTH ELECTRIC	ISSUE DATE	05. 30. 2005	E D .	ITI	O/®	研	1 發	部当
MACHINE INDUSTRY CO., LTD.	PAGE	4 OF 11				20	10.09	9 23


MODEL: A2179-HBT

P/N : TC.GN

PERFORMANCE CURVES

STATIC PRESSURE

mm-H₂O Inch-H₂O



				淡上
建準電機工業股份有限公司	SPEC.NO	A17000790G-00	REVISION I	OATE 09. 15. 2010
SUNONWEALTH ELECTRIC	ISSUE DATE	05. 30. 2005	EDITIO	解研發部3
MACHINE INDUSTRY CO., LTD.	PAGE	5 OF 11		2010.09.23


MATERIAL

2. Material

2-1. Frame : DIE-CAST ALUMINUM

2-2. Impeller : PC of UL 94V-0

DIMENSIONS




Air Flow Direction: Toward label side.

UNITS:mm

				燃工業 (2)
建準電機工業股份有限公司	SPEC.NO	A17000790G-00	REVISION I	DATE 09. 15. 2010
SUNONWEALTH ELECTRIC	ISSUE DATE	05. 30. 2005	EDITIO	學研發部 3
MACHINE INDUSTRY CO., LTD.	PAGE	6 OF 11		2010.09.23

Alveolate Motor



Thermal Cutout

With Capacitor



建準電機工業股份有限公司	SPEC.NO	A17000790G-00	REVISION	DA		09. 15.	2019
SUNONWEALTH ELECTRIC	ISSUE DATE	05. 30. 2005	EDITI	O/X	研	1 發	部当
MACHINE INDUSTRY CO., LTD.	PAGE	7 OF 11			20	10.09	23

Notes

I .SAFETY

- 1. DO NOT use or operate this fan in excess of the limitations set forth in this specification. SUNON is not be responsible for the non-performance of this fan and/or any damages resulting from its use, if it is not used or operated in accordance with the specifications.
- 2. SUNON recommends adding a protection circuit to the product or application in which this fan is installed, such as a thermo-fuse, or current-fuse or thermo-protector. The failure to use such a device may result in smoke, fire, electric shock by insulation degradation in cases of motor lock, motor lead short circuit, overload, or over voltage, and/or other failure.
- 3. SUNON recommends installing a protection device to the product or application in which this fan is installed if there is a possibility of reverse-connection between VDC (+) and GND (-). The failure to install such a device may result in smoke, fire, and/or destruction, although these conditions may not manifest immediately.
- 4. This fan must be installed and used in compliance with all applicable safety standards and regulations.
- 5. Use proper care when handling and/or installing this fan. Improper handling or installation of this fan may cause damage that could result in unsafe conditions.
- 6. Use proper care during installation and/or wiring. Failure to use proper care may cause damage to certain components of the fan including, but not limited to, the coil and lead wires, which could result in smoke and/or fire.
- 7. DO NOT use power or ground PWM to control the fan speed. If the fan speed needs to be adjusted, please contact Sunon to customize the product design for your application.
- 8. For critical or extreme environments, including non stop operation, please contact Sunon and we will gladly provide assistance with your product selection to ensure an appropriate cooling product for your application.

建準電機工業股份有限公司	SPEC.NO	A17000790G-00	REVISION D	AZE 09. 15. 2010
SUNONWEALTH ELECTRIC	ISSUE DATE	05. 30. 2005	EDITIO	解研發部 3
MACHINE INDUSTRY CO., LTD.	PAGE	8 OF 11		2010.09.23

Notes

II. SPECIFICATION MODIFICATION

- 1. SUNON offers engineering assistance on fan installation and cooling system design.
- 2. All changes, modifications and/or revisions to the specifications, if any, are incorporated in the attached specifications.
- 3. No changes, modifications and/or revisions to these specifications are effective absent agreement, by both Sunon and the customer, in writing.
- 4. This fan will be shipped in accordance with the attached specification unless SUNON and the customer have agreed otherwise, in writing, as specficied in Paragraph 3, above.

III. OTHER

- 1. When building your device, please examine thoroughly any variation of EMC, temperature rise, life data, quality, etc. of this product by shock/drop/vibration testing, etc. If there are any problems or accidents in connection with this product, it should be mutually discussed and examined.
- 2. Use proper care when handling this fan. Components such as fan holders or bearings may be damaged, if touched with fingers or other objects. Additionally, static electricity (ESD) may damage the internal circuits of the fan.
- 3. DO NOT operate this fan in proximity to hazardous materials such as organic silicon, cyanogens, formalin, phenol, or corrosive gas environments including, but not limited to, H₂S, SO₂, NO₂, or Cl₂.
- 4. SUNON recommends that you protect this fan from exposure to outside elements such as dust, condensation, humidity or insects. Exposure of this fan to outside elements such as dust, condensation, humidity or insects may affect its performance and may cause safety hazards. SUNON does not warrant against damage to the product caused by outside elements.

建準電機工業股份有限公司	SPEC.NO	A17000790G-00	REVISION I	AZE 09. 15. 2010
SUNONWEALTH ELECTRIC	ISSUE DATE	05. 30. 2005	EDITIO	一般 研發部 当
MACHINE INDUSTRY CO., LTD.	PAGE	9 OF 11		2010.09.23

Notes

- 5. This fan must be installed properly and securely. Improper mounting may cause harsh resonance, vibration, and noise.
- 6. Fan guards may prevent injury during handling or installation of the fan and are available for sale with this fan.
- 7. Unless otherwise noted, all testing of this fan is conducted at 25°C ambient temperature and sixty-five percent (65%) relative humidity.
- 8. DO NOT store this fan in an environment with high humidity. This fan must be stored in accordance with the attached specifications regarding storage temperature. If this fan is stored for more than 6 months, SUNON recommends functional testing before using.
- 9. SUNON reserves the right to use components from multiple sources at its discretion. The use of components from other sources will not affect the specifications as described herein.
- 10. The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.

VI. WARRANTY

This fan is warranted against all defects which are proved to be fault in our workmanship and material for one year from the date of our delivery. The sole responsibility under the warranty shall be limited to the repair of the fan or the replacement thereof, at SUNON's sole discretion. SUNON will not be responsible for the failures of its fans due to improper handing, misuse or the failure to follow specifications or instructions for use. In the event of warranty claim, the customer shall immediately notify SUNON for verification. SUNON will not be responsible for any consequential damage to the customer's equipment as a result of any fans proven to be defective.

				& 上
建準電機工業股份有限公司	SPEC.NO	A17000790G-00	REVISION I	09. 15. 2010
SUNONWEALTH ELECTRIC	ISSUE DATE	05. 30. 2005	EDITIO	一种一般部의
MACHINE INDUSTRY CO., LTD.	P A G E	10 OF 11		2010.09.23

Declaration of RoHS

Control declaration of environment-related substances/materials

1.In accordance with the Restriction of Hazardous Substances (RoHS) Directive, Sunon product with P/N: GN models have complied with law and discipline not to employ the forbidden substances, and restrict the allowable concentration of some limited substances deliberately in our components.

No		Substance	Criteria
1	CFCs & HCFCs (ozone depleting	ng substances)	Forbidden
2	Chlorinated Organic Solvent		Forbidden
		Plastic (Frame, Impeller, wire harness, etc.)	<100ppm
		Solder	<1000ppm
3	Lead and its compounds	Steel alloy	<3500ppm
		Aluminium alloy	<4000ppm
		Copper alloy	<4wt%
		Solder	<20ppm
4	Cadmium and its compounds	Parts composed of metals containing zinc (e.g. brass, zinc for die casting)	<100ppm
		Plastic	<5ppm
5	PBBs and PBDEs		Forbidden
6	PCB and PCT		Forbidden
7	CP, Short-chain Chlorinated pa	araffins C10-13, Cl≥48 wt%	Forbidden
8	Mirex		Forbidden
9	PCN		Forbidden
10	Hexavalent Chromium compou	inds	<100ppm
11	Mercury and its compounds		Forbidden
12	Asbestos		Forbidden
13	Organic Tin compounds		Forbidden
14	Azo compounds		Forbidden
15	TBBP-A in external case plastic	c parts of products (PCB is exempted)	<1000ppm
16	Nickel in external case parts, which	h are likely to result in prolonged skin exposure	<1000ppm

建準電機工業股份有限公司	SPEC.NO	A17000790G-00	REVISION I	ATE 09. 15. 2010
SUNONWEALTH ELECTRIC	ISSUE DATE	05. 30. 2005	EDITIO	爾研發部의
MACHINE INDUSTRY CO., LTD.	PAGE	11 OF 11		2010.09.23