

The EASYMIG 140 is a semi-automatic machine that combines MIG/MAG, cored wire and MMA welding processes. Thanks to its user-friendly interface, the voltage and wire speed settings are made easier. Ultra-light, it is easy to carry around. The EASYMIG 140 is recommended for welding steel, stainless steel and aluminium.

**3 in 1**


- MIG-MAG GAS
- MIG-MAG NO GAS
- MMA



### Ultra-light and portable

- 7.8 kg weight.
- Ergonomic handle.

### Easy set up



- Voltage set selection from 15 to 21 V.
- Wire speed selection from 3 to 9 m/min.

### Sturdy build quality

- Reinforced mechanical structure.
- Pads for shock and vibration absorption.

### Integrated wire feeder

- $\varnothing 100$  (1 kg) wire reels.
- 2 rollers motor
- Supplied rollers :
  - steel : 0.8
  - no gas : 0.9

### MIG/MAG Torch

- Supplied with a removable torch 150 A - 2.20 m fitted for steel.
- EURO torch for a fast assembly/disassembly.

### Simplified display



- 2 colour LED to display :
- Thermal protection.
  - Power up.

### MIG/MAG - MMA

- Wire diameter  $\varnothing 0.6$  mm to 0,8 mm.
- Électrode  $\varnothing 1.6$  mm à 3.2 mm.

### Polarity reversal cable

- For NO GAS welding.

### Features



Inverter technology to ensure an excellent welding current quality and a low electric consumption.



Can weld rutile electrodes . Antisticking (prevents electrode sticking at start).



Can weld :  
- MIG/MAG wire with gas  
- MIG/MAG cored wire without gas

### NO GAS ready to weld


This process allows :

- Welding with cored wire (requires polarity reversal).
- Allows outdoor welding (not wind. affected...)
- Increased portability due to absence of gas bottles.
- Ideal for outdoors work on thin metal sheets.

### Includes

- **Earth clamp**  
(cable 1.6 m / 16 mm<sup>2</sup>)
- **Electrode holder**  
(cable 1.6 m / 10 mm<sup>2</sup>)
- **Accessories bag**
  - Contact tip 0.9 mm.
  - Gas nozzle « gas ».
  - Tightening key for contact tips.
  - Gas tube 1 m.
  - 2 clamps for the gas tube.



50/60hz	AM	MMA I <sup>2</sup>	min▷max	ømm		100	Electronic Control	équipé d'origine / original equipment / originalausstattung / equipamiento de fabrica	EN60974-1 (40°C)				cm/kg	
				GAS	NO GAS				I <sub>A</sub> (60%)	X% (I <sub>2</sub> max)	I <sub>A</sub> (60%)	X% (I <sub>2</sub> max)		
230V 1~	16A	20▷120A	30▷140A	0.6 - 0.8	0.9	✓		0.8 - 0.9	0.8	80A	140A 15%	70A	120A 15%	38x16x35 / 7,8