
AC/DC 35W Enclosed Switching Power Supply MORNSUN®















FEATURES

- Universal 85 264VAC or 120 373VDC input voltage
- Accepts AC or DC input (dual-use of same terminal)
- Operating ambient temperature range: -30°C to +70°C
- Low standby power consumption, high efficiency
- High I/O isolation test voltage up to 4000VAC
- Low ripple & noise
- Output short circuit, over-current, over-voltage protection
- IEC/EN/UL62368, IEC/EN60335, GB4943, IEC/EN61558 safety approval
- Withstand 300VAC surge input for 5s
- Over-voltage class III (designed to meet EN61558)
- Operating altitude up to 5000m

LM35-20Bxx series is one of Mornsun's enclosed AC-DC switching power supply. It features universal AC input and at the same time accepts DC input voltage, cost-effective, low no load power consumption, high efficiency and high reliability. These converters offer excellent EMC performance and meet IEC/EN61000-4, CISPR32/EN55032, IEC/UL/EN62368, IEC/EN60335, GB4943, IEC/EN61558 standards and they are widely used in areas of industrial, LED, street light control, electricity, security, telecommunications, smart home etc.

Selection Guide							
Certification	Part No.*	Output Power(W)	Nominal Output Voltage and Current (Vo/Io)	Output Voltage Adjustable Range(V)	Efficiency at 230VAC (%) Typ.	Max. Capacitive Load (µF)	
UL, CE, CB, CCC	LM35-20B05	35	5V/7A	4.5-5.5	83	8000	
	LM35-20B12		12V/3A	10.2-13.8	87	1500	
	LM35-20B15	36	15V/2.4A	13.5-18	89	1000	
	LM35-20B24		24V/1.5A	21.6-28.8	88	750	

Note: *Use suffix "C" for terminal with protective cover and suffix "Q" for conformal coating.

Input Specifications						
Item	Operating Conditions	Min.	Тур.	Max.	Unit	
Innut Voltage Dange	AC input	85		264	VAC	
Input Voltage Range	DC input	120	-	373	VDC	
Input Voltage Frequency			47	-	63	Hz
L	115VAC		-	0.8		
Input Current	230VAC		-			0.6
l O	115VAC	0-1-1-44	-	30		Α
Inrush Current	230VAC	Cold start		50		
leakage current	240VAC		<0.75mA			
Hot Plug	Unavailable					

Output Specificatio	ns					
Item	Operating Conditions		Min.	Тур.	Max.	Unit
Outrout Voltage Assuracy	Full load range	5V	-	±2		
Output Voltage Accuracy	Full load range	12V/15V/24V	-	±1		
Line Regulation	Rated load			±0.5		%
	0% - 100% load	5V		±1		_
Load Regulation		12V/15V/24V	-	±0.5		
		5V		80		
Ripple & Noise*	20MHz bandwidth (peak-to-peak value)	12V/15V	-	120		mV
	(peak-10-peak value)	24V	-	150		
Temperature Coefficient			-	±0.03		%/℃

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.

AC/DC 35W Enclosed Switching Power Supply MORNSUN® LM35-20Bxx, LM35-20Bxx-C, LM35-20Bxx-Q Series

	0			%	
			0.3	W	
115VAC	8				
230VAC	30			ms	
Short Circuit Protection Recovery time <5s after the short circuit disappear. Hiccup, continuous, self-		us, self-recov	/ery		
	11	110%-200% lo, self-recovery			
5V	≤ 6.3VDC (Output voltage clamp or hiccup)				
12V	≤ 16.2VDC (Output voltage clamp or hiccup)				
15V	≤ 21.75VDC (Output voltage clamp or hiccup)				
24V	≤ 33.6VDC (Output voltage clamp or hiccup)				
	230VAC Recovery time <5s after the short circuit disappear. 5V 12V 15V	115VAC 8 230VAC 30 Recovery time <5s after the short circuit disappear. Hiccord 11 5V ≤ 6.3VDC 12V ≤ 16.2VDC 15V ≤ 21.75VDC ≤ 21.75VDC 15V ≤ 21.75VDC 15V 115V 115V	115VAC 8 230VAC 30 Recovery time <5s after the short circuit disappear. Hiccup, continuo 110%-200% lo, 5V ≤ 6.3VDC (Output volto 12V ≤ 16.2VDC (Output volto 15V ≤ 21.75VDC (Output volto 15V 5 5 7 15V 5 7 15V 5 7 15V 7 15	0.3 115VAC 8 230VAC 30 Recovery time <5s after the short circuit disappear. Hiccup, continuous, self-recovery 5V ≤ 6.3VDC (Output voltage clamp of 12V) 12V ≤ 16.2VDC (Output voltage clamp of 21.75VDC (Output voltage clamp	

Note: *The "Tip and barrel method" is used for ripple and noise test, output parallel 47uF electrolytic capacitor and 0.1uF ceramic capacitor, please refer to Enclosed Switching Power Supply Application Notes for specific information.

General	Specificatio	ns						
Item		Operating Conditions		Min.	Тур.	Max.	Unit	
Isolation	Input - 🕀							
	Input-output	Electric strength test for 1min., leakage current < 10mA			4000		-	VAC
	Output -		1250					
Insulation	Input - 🖶							
	Input - output	At 500VDC			100		-	MΩ
Resistance	Output -				100		-	
Operating Te	emperature				-30		+70	· °C
Storage Tem	perature				-40		+85	
Storage Hun	nidity	Non-condensing			-		95	%RH
Operating H	lumidity	Non-condensing			20	-	90	
Switching Fre	equency				-	65	-	kHz
		Operating	-30°C to -25°C	85VAC-100V AC	5			%/ ℃
Power Dera	ting	temperature derating	+50 ℃ to +70 ℃		2			
		Input voltage derating	85VAC - 100VAC		1.33			%/VAC
Safety Standard					IEC/EN/UL623 EN61558	68/IEC/EN6	0335/GB494	3/IEC/
Safety Certification			IEC/EN/UL62368/IEC/EN60338 EN61558		0335/GB494	3/IEC/		
Safety Class			CLASS		CLASS I	CLASSI		
MTBF		MIL-HDBK-217F@25℃			>300,000 h			

Mechanical Specifications				
Case Material	Metal (AL1100, SGCC)			
Dimension	99.00 x 82.00 x 30.00 mm			
Weight	170g (Typ.)			
Cooling Method	Free air convection			


Electromagnetic Compatibility (EMC)						
Emissions	CE	CISPR32/EN55032 CLASS B				
	RE	CISPR32/EN55032 CLASS B				
	Harmonic current	IEC/EN61000-3-2 CLASS A				
	ESD	IEC/EN 61000-4-2 Contact ±6KV /Air ±8KV	Perf. Criteria A			
	RS	IEC/EN 61000-4-3 10V/m	perf. Criteria A			
	EFT	IEC/EN 61000-4-4 ±2KV	perf. Criteria A			
Immunity	Surge	IEC/EN 61000-4-5 line to line ±2KV/line to ground ±4KV	perf. Criteria A			
	CS	IEC/EN61000-4-6 10 Vr.m.s	perf. Criteria A			
	Voltage dip, short interruption and voltage variation	IEC/EN61000-4-11 0%, 70%	perf. Criteria B			


MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.

AC/DC 35W Enclosed Switching Power Supply MORNSUN® LM35-20Bxx, LM35-20Bxx-C, LM35-20Bxx-Q Series


Product Characteristic Curve






Note: ①With an input voltage between 85-100VAC and a DC input between 120-140VDC the output power must be derated as per the temperature derating curves:


@This product is suitable for applications using natural air cooling; for applications in closed environment please consult Mornsun FAE.






Dimensions and Recommended Layout

LM35-20Bxx、LM35-20Bxx-Q Series



AC/DC 35W Enclosed Switching Power Supply MORNSUN® LM35-20Bxx, LM35-20Bxx-C, LM35-20Bxx-Q Series

LM35-20Bxx-C Series



Note:

- 1. For additional information on Product Packaging please refer to www.mornsun-power.com. Packaging bag number: 58220118;
- 2. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%RH with nominal input voltage and rated output load;
- 3. The room temperature derating of 5° C/1000m is needed for operating altitude greater than 2000m;
- All index testing methods in this datasheet are based on our company corporate standards;
- In order to improve the efficiency at high input voltage, there will be audible noise generated, but it does not affect product performance and reliability;
- 6. We can provide product customization service, please contact our technicians directly for specific information;
- 7. Products are related to laws and regulations: see "Features" and "EMC";
- 8. The out case needs to be connected to the earth of system when the terminal equipment in operating;
- Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

Mornsun Guangzhou Science & Technology Co., Ltd.

Address: No. 5, Kehui St. 1, Kehui Development Center, Science Ave., Guangzhou Science City, Huangpu District, Guangzhou, P. R. China Tel: 86-20-38601850 Fax: 86-20-38601272 E-mail: info@mornsun.cn www.mornsun-power.com

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.