

tab P11 Pro

LIKE A PRO.

DO EVERYTHING LIKE A PRO WITH YOUR TAB P11 PRO.

Featuring a prominent metal unibody, one of the world's thinnest and most powerful Android™ tablets lets you tap into non-stop entertainment. Doubling as a great productivity device that also packs an optional first-class keyboard and Lenovo Precision Pen 2, you can now do more while on the go.



WHY YOU SHOULD BUY THE LENOVO TAB P11 PRO

Ultra-slim aluminum-alloy unibody



- 5.8 mm thinnest.
- ~485 g tablet only.

11.5" 2K OLED display




- 2560 x 1600 resolution
- Support of Dolby Vision™ and HDR10.
- 4-side narrow bezel.
- Up to 87% screen-to-display ratio.

Always user-facing stereo



- 4 JBL® speakers and reinforced with Dolby Atmos®.

Fast and powerful



- Powered with Qualcomm® Snapdragon™ 730G, Octa-Core processor

Secure, effortless login



- Fingerprint login or zero touch face unlock at your ease.

2-in-1 keyboard pack¹



- 4-point pogo-in keyboard with trackpad.
- Magnetic stand cover with built-in kickstand.

Lenovo Precision Pen 2¹



- Works with Lenovo Precision Pen 2.

Long battery life²



- Up to 15 hours usage.

¹ Optional, and needs purchased separately, depending on the actual configuration.
² All battery life claims are approximate. Actual battery performance will vary and depend on numerous factors including product configuration and usage, software, operating conditions, wireless functionality, power management settings, screen brightness and other factors. The maximum capacity of the battery will naturally decrease with time and usage.



WWW.LENOVO.COM

Lenovo™

tab P11 Pro

SPECIFICATIONS

DESIGN



Weight

~485 g (1.06 lbs)

Operating System

Android™ 10



Login Security

Fingerprint : Yes

Face Unlock : Yes

PERFORMANCE

Processor

Qualcomm® Snapdragon™ 730G, Octa-Core, up to 2.2GHz CPU Clock Speed

Audio

Dual Microphone Array + Smart Voice by DSP (Mid Field)

Speakers

Quad JBL® Speakers, Optimized with Dolby Atmos®

Memory

RAM + ROM¹ : 4 GB + 128 GB / 6 GB + 128 GB (uMCP²)

Card Slot : microSD™ Card; Expandable up to 256 GB and exFAT file up to 1 TB

Battery³

For ROW SKU

Type : Li-ion Polymer 
Capacity : 8400 mAh (Minimum) / 8600 mAh (Typical)

Video Playback Time : Up to 15 Hours

Web Browsing Time : Up to 8 Hours

Normal Productivity Usage : Up to 15 Hours

Display

Size : 11.5"
Resolution : 2560 x 1600
Screen : OLED
Color Gamut : 108% NTSC
Brightness : From 350 nits (manual) to 500 nits (automatic)⁴
Touch : 10-point Multitouch



Colors

Slate Grey, Platinum Grey



Card Slots

Type : Nano SIM +TF
Slots : Single SIM Card Slot



Buttons and Ports

Volume Up/Down Buttons
4-point Pogo-pin Connector for the Keyboard
Power Button (+Fingerprint Login)
USB Type-C™ 3.1 (Gen 1⁵)

CONNECTIVITY

Wireless Connectivity

WLAN : WiFi 802.11 a/b/g/n/ac, 2.4 GHz & 5 GHz

Bluetooth® : Bluetooth® 5.0

WiFi Direct : Yes

WiFi Display : Yes

GPS/Beidou : Yes

A-GPS : Yes

FM Radio : No

GLONASS : Yes



Bands Supported

For ROW SKU

GSM : B2/B3/B5/B8

UMTS : B1/B2/B5(B6/B19)/B8

FDD LTE : B1/B2/B3(expanded band 3)/B4/B5/B7/B8/B18/B19/B20/B26/B28a/B28b

TDD LTE : B38/B39/B40/B41

For PRC SKU

GSM : B2/B3/B5/B8

WCDMA : B1/B2/B5/B8

TD-SCDMA : B34/B39

FDD LTE : B1/B3/B5/B7/B8

TDD LTE : B38/B39/B40/B41⁶

CDMA/EVDO : BC0

Integrated Camera

Rear
13 MP Auto-Focus + 5 MP Fixed-Focus (120° wide FOV)



Front
8 MP Fixed-Focus + 8 MP Fixed-Focus

Sensors

Accelerometer (G) Sensor
Hall Sensor
E-Compass
Ambient L-Sensor
Gyroscope
TOF (time-of-flight) Sensor
Vibrator

SOFTWARE

Included Applications

ROW

- Bamboo Paper
- Squid
- Office
- OneNote
- Netflix
- Dolby Atmos®
- Dolby Vision™
- Google
- Gmail
- Google Chrome
- Google Photos
- Google PlayStore
- Google Kids Space

TUV Certified Eye Protection

With special light and display technology development, Lenovo tablets ensure that the display lowers harmful blue light when appropriate to reduce strain on the eyes.



WHAT'S IN THE BOX*

- Lenovo Tab P11 Pro
- 10V/2A Charging Adapter
- Type-C™ Charging Cable
- SIM Pin
- Safety, Warranty, & Quick Start Guide
- Warranty Card

* The in-box items could vary with different configuration.

WANT MORE?

Lenovo Tab M10 FHD Plus (2nd Gen)



WWW.LENOVO.COM



Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, Yoga. Google and the Google logo are trademarks of Google Inc. Android is a trademark of Google Inc. Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi and Xeon Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors including system settings and usage. ©2020 Lenovo. All rights reserved.

ACCESSORIES



Lenovo Folio Case



Lenovo Keyboard Pack for P11 Pro



Lenovo Smart Charging Station 2



Lenovo Precision Pen 2

RECOMMENDED LENOVO SERVICES

Warranty Extensions (1-to-3 Years Total Duration)* The fixed-term, fixed-cost service helps accurately budget for PC expense, protect your valuable investment and potentially lower the cost of ownership.

Accidental Damage Protection* Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops or damage to the integrated screen.

* Not available in all countries.



Lenovo™