



ITEM NO. :	ITEM NO. :	LENGTH
29212c356b	767002S, 02	2000+100/-0
29212c356a	767002S, 11	1000+100/-0

NOTE:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 300V 0.01S 10MΩ;
 - Contact resistance:2Ω Max;
 - Data: 5Gbps max
- ROHS 2.0 and REACH
- PRINTING: HIGH SPEED USB 3.1 CABLE E***** 兄 AWM STYLE 20276 80°C 30V VW-1
- Operation temperature:-10°C ~+60°C
Storage temperature:-20°C ~ +75°C
Operation humidity:10%~85%
Storage humidity:10%~85%

MATERIAL LIST:

⑤	MOLDED	45P BLACK PVC	2	
④	MOLDED	LDPE	2	
③	USB A TYPE	USB 3.1 C /M Solder Type, Blue PBT Insulation, The Pin Gold Plated 15U", the shell nickel-plated With PCB board	1	
②	USB A TYPE	USB 3.1 C /F Solder Type, Blue PBT Insulation, The Pin Gold Plated 15U", the shell nickel-plated With PCB board	1	
①	CABLE	USB3.1 CABLE (1P*34AWG+D+AL+MY)*4C+1P*32AWG+4C*32AWG+2C*26AWG+F+MY+AB +Jacket PVC Black OD:4.2±0.2MM	1	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK
		NEW	2020. 12. 22	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

CUSTOMER	CN	ITEM NO.	
PRODUCT NAME	USB 3.1 C male to female	ITEM NO.	UNIT MM
DRAWNBY	CHECKBY	APPOBY	DATE
CoCo	Alvan		2020. 12. 22