



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Unit Color:	Dark Grey
Body Type:	Stainless Steel + PC
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Rated Load:	Max 40W
Dimension:	Ø148x900mm

POLE LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 8629 - 1662

[View more details](#)



FEATURES

- Traditional garden lamps designed to meet modern day requirements
- Strong and sturdy Stainless Steel + PC body
- Offering IP44 Ingress protection
- Compatible with E27 holder type (Fitting only - lamp not included)
- Suitable for gardens, patio, pathways etc.



PACKAGING

Gross Weight (Kgs): 1.06
Unit CBM: 0.01944
Dimension: Ø148x900mm

MASTER BOX PACKAGING

Box Qty: 6
Qty Per Pallet: 72
Length (Box) mm: 150
Width (Box) mm: 160
Height (Box) mm: 810

LISTING DETAILS

Commodity Code: 9405109890
Ean Code: 3800157652513