

Presentation System

















Receiver CAN support screen mirroring from iOS / Mac / Android / Windows / Chromecast





No need to use Transmitter for mobile / Tablet / MacBook





Long-range wireless connection up to 100ft (30 meters) (L.O.S)





Computer screen / TV /Projector





For most laptop screen output





Up to 32 wireless transmitters can be connected to one receiver (Additional TX required)









It also enables powerful dual split-screen mode, allowing attendees to share and compare graphs and charts side-by-side for a more effective discussion.






Control the flow of presentations at your fingertips.

Transmitter Box

LED Indication



Receiver Box

I/O Descriptions



Transmitter LED Status			
	Activate Host Standby w/o source input Main LED: OFF Host LED:Green ON		Activate Guest Standby w/o source input Main LED: OFF Guest LED:Red ON
0	Activate Host & in projecting Main LED:White ON Host LED:Green ON		Host received request of projection Host LED: Green FLASH
	Guest standby w/o Projecting Main LED:Red ON Guest LED:Red ON		Host standby w/o projecting Main LED:Red ON Host LED: Green ON
	Guest send request of projection and wait for allow Main LED:Red FLASH Guest LED:Red ON		 Under connection Pairing/TX OTA Fail to connection (blinking over 1 minutes)
	Activate Guest & in projecting Main LED:White ON Guest LED:Red ON		Pairing done Main LED:White ON Host LED: OFF
	Transmitter OTA Completed Main LED:White FLASH Host LED: OFF		Transmitter OTA Fail Main LED:Red FLASH Host LED: OFF



Box 70 ACTIVAL COLOR COL

CLASSROOM

A wireless connection from attendees' devices to a shared displayer would avoid the need for complex configuring and cabling.

MEETING ROOM

You can share BYOD content effortlessly with just one click in huddle rooms and many other types of meeting spaces.

Specification

Output Resolution	1920x1080@60Hz
I/O	HDMI out
	USB type A
	DC 5V
	Ethernet
WiFi Protocol	802.11a/n/ac
WiFi Frequency	5GHz: 5180MHz~5240MHz
Power	RX:DC 5V, 2A / TX:5V, 0.9A
Max.transmission distance(in meter)	30 meter (L.O.S)
Ethernet	10/100/1000M
LED Indication	Power, Ethernet, WiFi status, USB