



[Alcoswitch](#) | [Alcoswitch PKX](#)

TE Internal #: 1-1437625-3

Alcoswitch PKX, Switch Knobs, Knob, Phenolic, Ribbed Knob Design, .25in [6.35mm] Shaft Size, 1.576in [40mm] Switch Knob Diameter, Black, White Square

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**

Switch Knob Material: **Phenolic**

Knob Design: **Ribbed**

Shaft Size: **6.35 mm [.25 in]**

Switch Knob Diameter: **40 mm [1.576 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	Without
Spinner	Without
Spin Plate	Without
Knob Design	Ribbed

Body Features

Switch Knob Material	Phenolic
Switch Knob Color	Black

Dimensions

Shaft Size	6.35 mm[.25 in]
Switch Knob Diameter	40 mm[1.576 in]

Identification Marking

Indicator Style	White Square
Indicator Location	Top

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2018 (181) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | **Alcoswitch PKX**



Switch Knobs(4)

Customers Also Bought




TE Part #1-644042-2
 Nylon Gold Plated Receptacle: 2.54 mm, With Mating Alignment, MTA 100



TE Part #330896-2
 PIDG RING TONGUE TERMINALS




TE Part #322704
 TERMINAL,SOLIS R 4 3/8




TE Part #31763
 KNIFE DISCONNECT,STD B 16-14



TE Part #5413558-3
 BNC RF Connector: Male (Jack), Right-angle, 75 Ohm, 2 Ghz



TE Part #4-643813-7
 Nylon Tin Plated Receptacle: 2.54mm, With Mating Alignment, MTA 100



TE Part #31762
 KNIFE DISCONNECT,STD B 22-16



TE Part #45449
 DAHT PG 22-16 ASSY



TE Part #1-1437625-2
 PKX110B1/4=KNOB BLACK MATTI



TE Part #1-1437625-5
 PKX50B1/8=KNOB BLACK MATT

Documents

Product Drawings

[PKX130B1/4=KNOB BLACK MATTI](#)

English

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English