

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.



LITHIUM-BATTERY CR1632, 3.0 V/130 mAh

Item No.:	Pcs per pack
2377647	5
2377493	10

TECHNICAL DATA


Type:	CR1632
Classification:	Non-rechargeable
Chemical system:	Lithium/Manganese Dioxide (Li/MnO ₂)
Nominal voltage:	3.0 V
Weight (approx.)	1.75 g
Capacity:	130 mAh
Loading:	30 kΩ (20 ± 2 °C, 55 ± 20 % RH)
Cut-off voltage:	2.0 V
Operating conditions:	-18 to +50 °C +10 to +35 °C (recommended)
Storage conditions:	0 to +30 °C, 55 ± 20 % RH
Heavy metals:	Hg ≤ 5 ppm, Cd ≤ 20 ppm, Pb ≤ 40 ppm

For performance and safety, observe the operating / storage conditions. Capacity varies depending on the applied load, temperature, and cut-off voltage.




PERFORMANCE CHARACTERISTICS

DISCHARGE



DIMENSIONS (mm)



Dimension	Min.	Max.
Ø	15.8	16.0
H	3.0	3.2