

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.



CR1616 BUTTON CELL LITHIUM

Item No.:	Pcs per pack
2378999	5
2377710	10


TECHNICAL DATA

Type:	CR1616
Classification:	Non-rechargeable
Chemical system:	Lithium/Manganese Dioxide (Li/MnO ₂)
Nominal voltage:	3.0 V
Weight (approx.)	1.2 g
Capacity:	50 mAh
Loading:	30 kΩ (20 ±2 °C, 35 - 75% RH)
Cut-off voltage:	1.2 V
Operating conditions:	-18 to +50 °C, 55 ±20 % RH
Storage conditions:	0 to +30 °C, 55 ±20 % RH
Heavy metals:	No added mercury (Hg), Cadmium (Cd), or Lead (Pb)

For performance and safety, observe the operating / storage conditions. Capacity varies depending on the applied load, temperature, and cut-off voltage.



DIMENSIONS (mm)



Designation	CR1616
Outer Diameter	15.7~16.0
Total Height	1.4~1.6

DISCHARGE PERFORMANCE

