

416MA501P ✓ ACTIVE

Citec | Citec 416

TE Internal #: 1-1623893-0

Citec 416, Trimmer Potentiometers, Through Hole - Solder Termination Method to Printed Circuit Board, Radial-Leaded, 8.1 x 6.8 x 3.5 mm

[View on TE.com >](#)



Passive Components > Resistors > Trimmer Potentiometers



Termination Method to Printed Circuit Board: **Through Hole - Solder**

Passive Component Lead Type: **Radial-Leaded**

Passive Component Dimensions: **8.1 x 6.8 x 3.5 mm**

Passive Component Tolerance: **.2 %**

Sealing Requirement: **Semi-Sealed**

Features

Product Type Features

Sealing Requirement	Semi-Sealed
Rotary Turn Type	Continuous
Element Type	Cermet

Configuration Features

Number of Turns	1
Adjustment Location	Top
Adjustment Method	Cross Slot

Electrical Characteristics

Passive Component Tolerance	.2 %
Resistance Value	500 Ω
Power Rating	.2 W
Resistance Class	Up to 1k Ω

Body Features

Passive Component Lead Type	Radial-Leaded
Product Orientation	Horizontal

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Dimensions

Passive Component Dimensions

8.1 x 6.8 x 3.5 mm

Usage Conditions

Temperature Coefficient

±250 ppm/°C

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)
 Candidate List Declared Against: JUN 2020 (209)
 SVHC > Threshold:
 Not Yet Reviewed

Halogen Content

BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.

Solder Process Capability

Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts





TE Part # 1623894-4
416P 10K

Also in the Series | Citec 416



Trimmer Potentiometers(40)

Customers Also Bought



TE Part #1-1393243-0
RTE24024



TE Part #1-1623893-4
416M 500K



TE Part #1623549-1
CRG1206 1% 680R




TE Part #1-86177-5
16 MODIV HSG COMP DR .100CL



TE Part #9-2176310-3
RP 1E 0.1W 976R 0.1% 25PPM 1K RL



TE Part #1478769-2
ANTI-VIB NYLON GLD 16MM BLK



TE Part #1-1623893-2
416M 50K



TE Part #1-480303-2
03P CMNL PLUG HSG F/H RED



TE Part #1-1623893-1
416M 5K



TE Part #1-1623893-3
416M 200K



Documents

Product Drawings

[416M 500R](#)

English

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Type 416 Series Economy Trimmers](#)

English