

PKS90B101/4 ✓ ACTIVE

[Alcoswitch](#) | [Alcoswitch PKS](#)

TE Internal #: 1437625-6

Alcoswitch PKS, Switch Knobs, Knob, Phenolic, Straight Knurl Knob Design, .25in [6.35mm] Shaft Size, 1.42in [36.1mm] Switch Knob Diameter, Black

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**

Switch Knob Material: **Phenolic**

Knob Design: **Straight Knurl**

Shaft Size: **6.35 mm [.25 in]**

Switch Knob Diameter: **36.1 mm [1.42 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	With
Spinner	Without
Spin Plate	Without
Knob Design	Straight Knurl

Body Features

Switch Knob Material	Phenolic
Switch Knob Color	Black

Dimensions

Shaft Size	6.35 mm[.25 in]
Switch Knob Diameter	36.1 mm[1.42 in]

Identification Marking

Indicator Style	1-10 Numerals
Indicator Location	On Skirt

Other

Comment	Top spun aluminum inlay
---------	-------------------------



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Also in the Series | [Alcoswitch PKS](#)



Switch Knobs(7)

Customers Also Bought



TE Part #M3021-000005-250PG
Pressure Transducers Readily Available




TE Part #1461404-6
STD OEG Miniature PCB OJ/OJE Pow Relays




TE Part #1611004-6
DP CONTACTORS, 2 POLE



TE Part #1879234-4
SMD Power Resistor: 7 Watt, 200-2M Ohm



TE Part #1487594-2
USB, A-B, 28/28, BLACK, 0.25M



TE Part #1487595-1
USB, A-B, 28/26, BLACK, 1.0M



TE Part #2-1623708-3
RGP0207CH 5% 130M



TE Part #1546349-2
CPC CABLE CLAMPS



TE Part #1437625-5
PKS90B1/4=KNOB PLASTIC W/SKIRT



TE Part #1520237-2
7320K3=8 AMP TOGGLE SWITCH

Documents

Product Drawings

[PKS90B101/4=KNOB PLASTIC W/SKI](#)

English

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English