



Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 3 Watt, 1% Tol



Resistor Type: **Power Resistor**

Number of Terminations: **2**

Package Size Code: **2512**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

[All SMD Power Resistor: 3 Watt, 1% Tol \(140\)](#)

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Power Resistor
Package Size Code	2512
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	1 %
Resistance Class	1kΩ – 1MΩ
Resistance Value	510K Ω
Power Rating	3 W

Termination Features

--



Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	6.35 x 3.2 x .55 mm
------------------------------	---------------------

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # CAT-C339-A76B
SMD Power Resistor: 3 Watt, 1% Tol



TE Part # CAT-C339-A76C
SMD Power Resistor: 3 Watt, 5% Tol

Also in the Series | CGS 3522




Surface Mount Resistors(220)

Customers Also Bought



TE Part #206043-3
CPC SERIES 1



TE Part #2176071-7
SMD Power Resistor: 2 Watt, 3521 Series




TE Part #1625854-4
1206 PROBE PAD



TE Part #1-66101-6
III+ SKT,18-16,TIN-LEAD,SMPACK



TE Part #2-103639-5
02 MTE HDR SRST LATCH .100CL



TE Part #2176392-8
RQ 1206 158K 0.1% 10PPM 5K RL




TE Part #YDTS20F25-37PCC001
D38999: Square Flange, 25-37 insert



TE Part #182663-1
CPC CABLE CLAMPS EMEA



TE Part #1623939-2
SC10-10-0549-10 1000UH AMMO 1000



TE Part #1445730-1
STRN RELIEF ASY,STRT SIZE 8



Documents

Product Drawings

3522 510K 1% 3W

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2176232-5_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2176232-5_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2176232-5_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD POWER RESISTORS - TYPE 3522 SERIES

English