



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **General Purpose Resistor**

Number of Terminations: **2**

Package Size Code: **1206**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	General Purpose Resistor
Package Size Code	1206
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	200 V
Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	1.8 Ω
Power Rating	.25 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	3.1 x 1.55 x .55 mm
------------------------------	---------------------

Usage Conditions



Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1623097-1
CRG0805 1% 10K

TE Part # 1623404-1
CRG1206 1% 10K

TE Part # 1622829-1
CRG0603 1% 10K

TE Part # 1676480-1
CRG0402 1% 100K



TE Part # 1-1622826-8

CRG0402 5% 1K0

Also in the Series | Neohm CRG

Surface Mount Resistors(647)

Customers Also Bought

TE Part #1888321-2

Shielded Receptacle Assembly,

TE Part #1-5120534-1

Free Height Plug Connector: Board-Board, Vertical, 64, 1mm

TE Part #2102092-1

Fortis Zd 2Pr 10Col Vert End Mod Assy

TE Part #2102086-1

Fortis Zd 2Pr 10Col R/A Left Module Assy

TE Part #2102087-1

Fortis Zd 2Pr 10Col R/A Cent Module Assy

TE Part #1879276-2

RP 2A 5K62 0.1% 15PPM 1K RL

TE Part #2149730-2

SFP+ Enhanced 1x4 Cage, PCI Heatsink

TE Part #5767044-4

MICTOR,R/A,RECPT,062,152,ASY

TE Part #1676269-1

RN 0805 261R 0.1% 10PPM CUT LENGTH

TE Part #1624032-1

SC30-10-2547-10 680UH AMMO 1000



Documents

Product Drawings

CRG1206 1% 1R8

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1623454-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1623454-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1623454-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Thick Film Chip Resistors - Type CRG series

English