



Sigma | Sigma SC

TE Internal #: 1624055-2

Sigma SC, High Frequency & RF Inductors, Radio Frequency, Through Hole - Solder, Ammo Packed, 7 x 2.8 mm, 10 Passive Component Tolerance

[View on TE.com >](#)

Passive Components > Inductors > High Frequency & RF Inductors



Inductor Type: **Radio Frequency**

Termination Method to Printed Circuit Board: **Through Hole - Solder**

Packaging Method: **Ammo Packed**

Passive Component Dimensions: **7 x 2.8 mm**

Passive Component Tolerance: **10 %**

**Features**

**Product Type Features**

Inductor Type	Radio Frequency
Element Type	Wire Wound
Package Size Code	SC30

**Electrical Characteristics**

Self Resonant Frequency	.25 GHz
Passive Component Tolerance	10 %
Inductance	.82 $\mu$ H
Current Rating (Max)	455 mA
DC Resistance	.85 $\Omega$

**Body Features**

Passive Component Lead Type	Axial-Leaded
-----------------------------	--------------

**Termination Features**

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

**Dimensions**

Passive Component Dimensions	7 x 2.8 mm
------------------------------	------------

**Usage Conditions**

Operating Temperature Range	-55 – 100 $^{\circ}$ C
-----------------------------	------------------------



### Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

### Other

Inductor Quality Factor	28
-------------------------	----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

TE Part # 1624009-2  
SC30-10-2513-10 1UH AMMO 1000




TE Part # 1623937-3  
SC10-10-0525-10 10UH AMMO 1000

TE Part # 1624001-3  
SC30-10-2537-10 100UH AMMO 1000


TE Part # 1624023-2  
SC30-10-2519-10 3.3UH AMMO 1000



## Also in the Series | Sigma SC



## Customers Also Bought





## Documents

### Product Drawings

[SC30-10-2512-10 0.82UH AMMO 1000](#)

English

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1624055-2\\_BA.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1624055-2\\_BA.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1624055-2\\_BA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[Axial Leaded Power Inductors - Type SC10, SC15, SC30 Series - Tyco Electronics Passives](#)

English