



CGS | CGS TL

TE Internal #: 1625826-9

CGS TL, Surface Mount Resistors, Low Ohmic Resistor, 2 Termination, 1206, Taped & Reeled, 1 %, Foil, Resistance Class Up to 1kΩ, .09 Ω, .25 W

[View on TE.com >](#)

Passive Components > Resistors > Surface Mount Resistors > Metal Chip Resistor: Current Sense



Resistor Type: **Low Ohmic Resistor**

Number of Terminations: **2**

Package Size Code: **1206**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

[All Metal Chip Resistor: Current Sense \(56\)](#)

## Features

### Product Type Features

Product Type	Fixed Resistor
Resistor Type	Low Ohmic Resistor
Package Size Code	1206
Element Type	Foil

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	.09 Ω
Power Rating	.25 W

### Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

### Dimensions

Passive Component Dimensions	3.2 x 1.6 x .6 mm
------------------------------	-------------------



### Usage Conditions

Temperature Coefficient	±75 ppm/°C
-------------------------	------------

### Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Compatible Parts



## Also in the Series | CGS TL




Portable Crimp Tools(4)



Surface Mount Resistors(56)


## Customers Also Bought



TE Part #1-216604-0  
2X10P HV190FEDERLEI



TE Part #1623094-1  
CRG0603 ZEROHM



TE Part #142270-1  
CONNECTOR SHUNT 2 P



TE Part #1571294-2  
SWITCH,TACT,SMT,SEALED,T&R



TE Part #1622931-1  
CRG0603 1% 390R



TE Part #9-1614353-7  
RN 0603 2K32 0.1% 10PPM 1K RL



TE Part #1-2176313-0  
RP 1E 0.1W 165K 0.1% 25PPM 1K RL



TE Part #1565917-4  
DDR2 SO DIMM Sockets



TE Part #1-1625826-2  
Metal Chip Resistor: Current Sense



TE Part #1624097-8  
3615A-10-3533-10 47UH

## Documents

### Product Drawings

TL2B R09 1%

English

### Datasheets & Catalog Pages

1309350\_PASSIVE\_COMPONENT

English



## SMD Low Ohmic - Current Sense Resistors - Type TL Series - Tyco Electronics Passives

English

---

### Product Environmental Compliance

#### TE Material Declaration

English