



Passive Components > Resistors > Surface Mount Resistors > Metal Chip Resistor: Current Sense



Resistor Type: **Low Ohmic Resistor**

Number of Terminations: **2**

Package Size Code: **1575**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

[All Metal Chip Resistor: Current Sense \(49\)](#)

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Low Ohmic Resistor
Package Size Code	1575
Element Type	Metal Strip

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	.002 Ω
Power Rating	4 W

Termination Features

--



Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	15.2 x 7.5 x .9 mm
------------------------------	--------------------

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts






TE Part # CAT-C339-T547B

Metal Chip Resistor: Current Sense



TE Part # 2176077-7

TLRS1575 3.0W R005 1% 100PPM 2K RL



TE Part # 2176077-6

TLRS1575 6.0W R0004 1% 50PPM 2K RL

Also in the Series | CGS TLR



Surface Mount Resistors(51)

Customers Also Bought



TE Part #1-1827864-8

DYNAMIC 1200 REC AND TAB HSG



TE Part #1-770873-1

03P MINI UMNL HDR ASSY AU LF



TE Part #1622211-1

LR0204 1% 2K7




TE Part #1622209-1

LR0204 1% 2K2




TE Part #1622239-1

LR0204 1% 43R




TE Part #1624323-3

UPW50 0.1% 5PPM 10K



TE Part #1-1624323-1

UPW50 0.1% 5PPM 2K0



TE Part #8-1440000-6

STD OEG Miniature PCB OJT Power Relays



TE Part #1376607-1

TH/.025 CONNECTOR SYSTEM, RECPT AND TAB



TE Part #1624097-1

3615A-10-3525-10 10UH



Documents

Product Drawings

TLRS1575 4.0W R002 1% 100PPM 2KRL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2176077-3_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2176077-3_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2176077-3_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Surface Mount Shunt Resistor - Type TLRS series

English