



Passive Components > Resistors > Surface Mount Resistors > Metal Chip Resistor: Current Sense



Resistor Type: **Current Sensing Resistor**
Number of Terminations: **2**
Package Size Code: **2010**
Packaging Method: **Taped & Reeled**
Passive Component Tolerance: **5 %**

[All Metal Chip Resistor: Current Sense \(152\)](#)

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Current Sensing Resistor
Package Size Code	2010
Element Type	Foil

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	5 %
Resistance Class	Up to 1kΩ
Resistance Value	.047 Ω
Power Rating	.75 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	5 x 2.5 x .55 mm
------------------------------	------------------



Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C339-T547A
Metal Chip Resistor: Current Sense



Also in the Series | CGS TLM

Surface Mount Resistors(152)

Customers Also Bought

TE Part #2-2176053-2
Thick Film Resistor: Current Sense

TE Part #154N-005G-RT
MEDIA ISOLATED PRESSURE STOCK LIST

TE Part #1623804-8
Wirewound Resistor: Horizontal Mount

TE Part #1676199-2
RN 0805 15K 0.1% 10PPM 1KRL

TE Part #1625886-4
1W SM M/OX 5% 330R

TE Part #1-2176157-3
Metal Chip Resistor: Current Sense

TE Part #1-215460-6
MICRO-MATCH FEM.SE

TE Part #1614898-2
CPF0805 15K 0.1% 25PPM 5K RL

TE Part #1614351-3
RN 0603 1K5 0.1% 10PPM CUT LENGTH

TE Part #ZPF000000000205970
951-07 RC 10-6 P 50-395

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2176157-9_BA.2d_dxf.zip

English

Customer View Model



[ENG_CVM_CVM_2176157-9_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176157-9_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMD Current Sense Metal Chip Resistor](#)

English