



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **High Value/High Voltage Resistor**

Number of Terminations: **2**

Package Size Code: **2512**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	High Value/High Voltage Resistor
Package Size Code	2512
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	200 V
Passive Component Tolerance	1 %
Resistance Class	1kΩ – 1MΩ
Resistance Value	100K Ω
Power Rating	1 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	6.35 x 3.2 x .55 mm
------------------------------	---------------------

Usage Conditions

--	--



Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

Comment	Max overload voltage 1600V
---------	----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRGV2512F100K

Neohm CRGV, Surface Mount Resistors, High Value/High Voltage Resistor, 2 Termination, 2512, Taped & Reeled, 1 %, Thick Film



TE Part # 2-1879532-0
CRGV2512 5% 330K 1600V

TE Part # 3-1879530-3
CRGV1206 5% 2M2 1000V

TE Part # 3-1879530-4
CRGV1206 5% 2M4 1000V

TE Part # 2-1879537-6
CRGV2010 1% 1M0 3000V

TE Part # 4-1879537-3
CRGV2010 1% 1M5 3000V

Also in the Series | Neohm CRGV

Surface Mount Resistors(992)

Customers Also Bought

TE Part #2176157-3
Metal Chip Resistor: Current Sense

TE Part #1-1879450-4
Wirewound Resistor: Mineral, 2.5 Kw

TE Part #5-2172071-2
M12.FMLE.PNLREAR.ACODE.8P. PCBSTAND.STRT

TE Part #2-87215-3
46 MODII HDR DRST UNSHRD .100

TE Part #201356-3
MALE BLOCK 20 PL. MIN. RECT.

TE Part #1622712-1
LR2 1% 220K

TE Part #2-1415898-6
PCB Power Relay: 16 Amp, Inrush

TE Part #1622734-1
LR2 1% 33K



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1879539-9_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1879539-9_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1879539-9_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

High Voltage Thick Film Chip Resistors - Type CRGV series

English