



Relays, Contactors & Switches > Switches > Hardware & Seals

Switch Boot Accessory Type: **End Mounting Plates (Pair)**

Style: **Special**

Features

Product Type Features

Product Type	Accessory
Illuminated	No
Switch Boot Accessory Type	End Mounting Plates (Pair)
Style	Special

Configuration Features

End Mounting Plates (Pair)	Flanged with Mounting Holes
Tactile	No

Body Features

Seal Type	Dust Sealed
-----------	-------------

Mechanical Attachment

Attachment Method	Press-Fit, Snap-Together
-------------------	--------------------------

Housing Features

Housing Color	Black
Process Sealed	No

Usage Conditions

Oil-Tight	No
-----------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)

Candidate List Declared Against: JAN 2021
(211)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1437602-1
SMCL=replaces SMCBG


Customers Also Bought



TE Part #1469081-1
HMZD 3PR, RECEPTACLE ASSEMBLY




TE Part #1-2176093-2
RP 2A 0.25W 12K1 0.1% 25PPM 1K RL



TE Part #1437606-8
B9LS=SW CONN FOR SMC, PC TERM




TE Part #1-1879510-2
CRGH0805 1% 1K5 0.33W



TE Part #1623750-9
ER58 1K0 5% AMMO




TE Part #1-1614353-4
RN 0603 301R 0.1% 10PPM CUT LENGTH



TE Part #1-1437602-9
SMCD301AK=SW BI-DIR W/LIMIT ST



TE Part #1-1437602-5
SMCD131AK=SW BI-DIR W/LIMITS S



TE Part #1437536-5
DIP Socket: Standard, Screw Machine, Closed, Gold



TE Part #ZPF000000000000294
006-0910-12

Documents

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English