

CRGS1206J120R

✓ ACTIVE


TE Internal #: 2-2176245-6

Surface Mount Resistors, General Purpose Resistor, 2 Termination, 1206, Taped & Reeled, 5 %, Thick Film, Resistance Class Up to 1kΩ, 120 Ω, .6 W

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **General Purpose Resistor**

Number of Terminations: **2**

Package Size Code: **1206**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **5 %**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	General Purpose Resistor
Package Size Code	1206
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	200 V
Passive Component Tolerance	5 %
Resistance Class	Up to 1kΩ
Resistance Value	120 Ω
Power Rating	.6 W

Termination Features

Number of Terminations	2
------------------------	---



Surface Mount Resistor Termination Type

Solder

Dimensions

Passive Component Dimensions	3.1 x 1.55 x .55 mm
------------------------------	---------------------

Usage Conditions

Temperature Coefficient	±400 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRGS1206J120R

Surface Mount Resistors, General Purpose Resistor, 2 Termination, 1206, Taped & Reeled, 5 %, Thick Film, Resistance Class Up to 1kΩ, 120 Ω, .6 W



TE Part # 2-2176245-5
CRGS1206 5% 100R

TE Part # 2-2176245-7
CRGS1206 5% 150R

Customers Also Bought

TE Part #1-1415898-6
PCB Power Relay: 16 Amp, Inrush

TE Part #1-1393210-8
PCB Power Relay: 30 Amp, Monostable DC

TE Part #1-1470364-5
AMP HPI 1.0MM RECEPTACLE HOUSINGS

TE Part #1-1825027-4
FSMRA5JH04=R/A,TACT PB SW,160G

TE Part #1393219-6
PE014012

TE Part #1614902-2
CPF0805 1K0 0.1% 25PPM 5K RL

TE Part #1614902-3
CPF0805 1K5 0.1% 25PPM 5K RL

TE Part #1-1625999-0
Power Resistors: Aluminum Housed, HSC

TE Part #Y5015-000000100020
PLUG WITH RFI GROUNDING - FEMALE - CIRH

TE Part #1393240-7
RT314730

Documents

Product Drawings

CRGS1206 5% 120R

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2176245-6_BA.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-2176245-6_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2176245-6_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMD Anti-Surge Thick Film Chip Resistor - Type CRGS Series - Tyco Electronics Passives](#)

English