



Passive Components > Resistors > Potentiometers

Power Rating: **2 W**Product Terminates To: **Printed Circuit Board**Product Mount Type: **Panel Mount**Passive Component Dimensions: **12.7 x 19.05 mm**Passive Component Tolerance: **10 %**

Features

Product Type Features

Element Type	Cermet
Sealing Requirement	Sealed
Rotary Turn Type	Single Turn

Configuration Features

Number of Turns	1
Sections	Single
Adjustment Location	Top
Adjustment Method	Shaft

Electrical Characteristics

Power Rating	2 W
Passive Component Tolerance	10 %
Resistance Value	22K Ω
Resistance Class	1k Ω – 1M Ω

Body Features

Shaft Style	Plain
Product Orientation	Vertical

Termination Features

Product Terminates To	Printed Circuit Board
-----------------------	-----------------------



Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Dimensions

Passive Component Dimensions	12.7 x 19.05 mm
	1 in

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1625931-3
MCU 47K 10% 1"PL

TE Part # 3-1625931-1
MCU 10K 10% 1"PL

TE Part # 3-1625931-0
MCU 4K7 10% 1"PL

TE Part # 2-1625931-6
MCU 100R 10% 1"PL

TE Part # 2-1625931-8
MCU 1K 10% 1"PL

TE Part # 3-1625931-9
MCU 220R 10% 1"PL

TE Part # 2-1625931-7
MCU 470R 10% 1"PL

TE Part # 2-1625931-9
MCU 2K2 10% 1"PL

TE Part # 3-1625931-4
MCU 220K 10% 1"PL

TE Part # 3-1625931-8
MCU 47R 10% 1"PL

TE Part # 3-1625931-5
MCU 1M 10% 1"PL

TE Part # 3-1625931-7
MCU 22R 10% 1"PL

TE Part # 3-1625931-6
MCU 10R 10% 1"PL

TE Part # 2-1625931-5
MCU 100K 10% 1"PL

TE Part # 2-1625931-4
MCU 470K 10% 1"PL

TE Part # 1-1625931-8
MCU 4K7 10% 5/8"SL

TE Part # 4-1625931-2
MCU 10R 10% 5/8"SL

TE Part # 1625930-7
MC1 10K 10% 25MM PL

Also in the Series | **Citec M**



Potentiometers(18)

Customers Also Bought




TE Part #156667-1
PIDG FASTON RECPT QUICK DISCONNECTS



TE Part #1393827-2
CRADLE RELAY ACCESSORY



TE Part #1-1623819-4
SBL4 R051 5%



TE Part #1-215919-6
AMP-LATCH 15.2 HIGH TAPE



TE Part #1623463-1
CRG1206 1% 22R




TE Part #DRC16-24SA-P013
DEUTSCH DRC HOUSINGS



TE Part #1-174954-1
SIGNAL HEADER



TE Part #1-1393304-1
V23134J1053D642-EV-CBOX



TE Part #1-1478408-0
BNC Str Plg PS 75Ohm Silver URM70



TE Part #1393280-6
V23086C1001A403

Documents

Product Drawings

[MCU 22K 10% 1" PL](#)

English

CAD Files

Customer View Model

[ENG_CVM_3-1625931-2_P00K.3d_igs.zip](#)

English

Customer View Model



[ENG_CVM_3-1625931-2_P00K.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_3-1625931-2_P00K.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Spindle Operated Potentiometers - Type M Series - Tyco Electronics Passives](#)

English