



Alcoswitch

TE Internal #: 4-1437622-2

Switch Knobs, Knob, Aluminum, Straight Knurl Knob Design, .25in [6.35mm] Shaft Size, .5in [12.7mm] Switch Knob Diameter, Natural, Line

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**

Switch Knob Material: **Aluminum**

Knob Design: **Straight Knurl**

Shaft Size: **6.35 mm [.25 in]**

Switch Knob Diameter: **12.7 mm [.5 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	Without
Spinner	Without
Spin Plate	Without
Knob Design	Straight Knurl

Body Features

Switch Knob Material	Aluminum
Switch Knob Color	Natural

Dimensions

Shaft Size	6.35 mm[.25 in]
Switch Knob Diameter	12.7 mm[.5 in]

Identification Marking

Indicator Style	Line
Indicator Location	Side

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 4-1437622-6
KN500B1/4=KNOB BLACK KNURL 1/4

Customers Also Bought

TE Part #1-794107-0
22P MINI UMNL R/A HDR ASSY LF

TE Part #1-794106-0
20P MINI UMNL R/A HDR ASSY

TE Part #1-794105-0
18P MINI UMNL R/A HDR ASSY SN


TE Part #1-770967-0
03P MINI UMNL R/A HDR ASSY SN



TE Part #1-770970-0
08P MINI UMNL R/A HDR ASSY SN



TE Part #1-770858-0
10P MINI UMNL HDR ASSY SNDBL L



TE Part #1-796683-6
TERMI-BLOK PCB MOUNT 90 16P.



TE Part #2-2176416-0
9W STD M/OX 5% 330R



TE Part #1676281-1
RN 0805 2K05 0.1% 10PPM CUT LENGTH



TE Part #YHDP26-18-20SEL024
DEUTSCH HDP20 HOUSINGS

Documents

Product Drawings

[KN500A1/4=KNOB ALUM KNURL 1/4](#)

English

CAD Files

Customer View Model

[ENG_CVM_4-1437622-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_4-1437622-2_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_4-1437622-2_A.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Alcoswitch Products](#)

English