

KN5700B1/4 ✓ ACTIVE

Alcoswitch

TE Internal #: 5-1437622-7

Switch Knobs, Knob, Aluminum, Concentric Set with Straight Knurl
Knob Design, .25in [6.35mm] Shaft Size, .75in [19.1mm] Switch Knob
Diameter, Black

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**

Switch Knob Material: **Aluminum**

Knob Design: **Concentric Set with Straight Knurl**

Shaft Size: **6.35 mm [.25 in]**

Switch Knob Diameter: **19.1 mm [.75 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	Without
Spinner	Without
Spin Plate	Without
Knob Design	Concentric Set with Straight Knurl

Body Features

Switch Knob Material	Aluminum
Switch Knob Color	Black

Dimensions

Shaft Size	6.35 mm[.25 in]
Switch Knob Diameter	19.1 mm[.75 in]

Identification Marking

Indicator Style	Line
Indicator Location	Side

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1437622-2
KN501B1/4=KNOB BLACK KNURL 1/4


Customers Also Bought



TE Part #123329-000
Low Profile Heat Shrink Boots: Poly Mold, Lipped, Right Angle



TE Part #2-1617031-4
HFW1201K46M = M39016/6-209M



TE Part #1617749-2
FCA-210-0926M=M83536/9-026M



TE Part #242381-000
S03-05-R-9035-100



TE Part #225559-2
TNC RT ANG PLUG DUAL W/P TR



TE Part #SP1-4
CABLE ACTUATED POSITION STOCK LIST



TE Part #2-1617038-1
HMB1201K01M = M39016/22-009M



TE Part #1757827-4
AMPLIMITE, PLUG ASY, POSTD, 109, ZN, 4



TE Part #1616060-1
A931F=CONTACTOR, SPST-NC, 600A



TE Part #2-1617146-7
JMGACDD-26L = M39016/19-036L

Documents

Product Drawings

[KN5700B1/4=KNOB BLACK PAIR 1/8](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_5-1437622-7_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1437622-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1437622-7_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English