



Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 3 Watt, 5% Tol



Resistor Type: **Power Resistor**

Number of Terminations: **2**

Package Size Code: **2512**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **5 %**

[All SMD Power Resistor: 3 Watt, 5% Tol \(67\)](#)

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Power Resistor
Package Size Code	2512
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	5 %
Resistance Class	1kΩ – 1MΩ
Resistance Value	4.7K Ω
Power Rating	3 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	6.35 x 3.2 x .55 mm
------------------------------	---------------------



Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-C339-A76B
SMD Power Resistor: 3 Watt, 1% Tol

TE Part # CAT-C339-A76C
SMD Power Resistor: 3 Watt, 5% Tol



Also in the Series | CGS 3522

Surface Mount Resistors(220)

Customers Also Bought

TE Part #1-284512-2
12 POS TERMI-BLOK HDR 900 POLA

TE Part #1571634-1
TACT SWITCH,SMT,SOFT ACTUATOR

TE Part #1-1879336-7
CPF 0603 340R 1% 50PPM 1K RL

TE Part #825434-5
5P MOD II BRK AWAY HDR, 0.8AU, 1 ROW

TE Part #1-1825910-5
FSM8JAH=6MM TACT SWITCH, HIGH TEMP

TE Part #1825910-1
FSM2JLH=6MM TACT SWITCH, HIGH TEMP

TE Part #146281-2
02 MODII HDR SRST B/A .100CL

TE Part #1744427-2
EP Header Asy,Shrouded,2 Pos, GW

TE Part #1-1776275-0
Vertical Term Blk Side Wire En

TE Part #1-1775333-0
0.5mm FPC Connectors

Documents

Product Drawings

3522 4K7 5% 3W

English

Datasheets & Catalog Pages

SMD POWER RESISTORS - TYPE 3522 SERIES

English

35224K7JT

CGS 3522, Surface Mount Resistors, Power Resistor, 2 Termination, 2512, Taped & Reeled, 5 %, Thick Film, Resistance Class 1kΩ – 1MΩ, 4.7K Ω, 3 W

