

SMA-A0204FTDX6K8

✓ ACTIVE

TE Internal #: 6-2176315-0

Surface Mount Resistors, Precision Resistor, 2 Termination, 0204, Taped & Reeled, 1 %, Thin Film, Resistance Class 1kΩ – 1MΩ, 3.9K Ω, .4 W

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Package Size Code: **0204**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Precision Resistor
Package Size Code	0204
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	200 V
Passive Component Tolerance	1 %
Resistance Class	1kΩ – 1MΩ
Resistance Value	3.9K Ω
Power Rating	.4 W

Termination Features

Number of Terminations	2
------------------------	---

Surface Mount Resistor Termination Type

Metal Electrode Leadless Face (MELF)

Dimensions

Passive Component Dimensions	3.5 x 1.4 mm
------------------------------	--------------

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±50 ppm/°C

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SMA-A0204FTDX6K8

Surface Mount Resistors, Precision Resistor, 2 Termination, 0204, Taped & Reeled, 1 %, Thin Film, Resistance Class 1kΩ – 1MΩ, 3.9K Ω, .4 W



TE Part # 6-2176314-9
MELF SMA-A 10R 1% 50PPM 0102 0.3 W

TE Part # 3-2176315-2
MELF SMA_A 39K 0.1% 15PPM 0204 0.4W

TE Part # 2176316-5
MELF SMA_A 220R 0.1% 15PPM 0207 1W

TE Part # 9-2176315-8
MELF SMA-A 1M0 1% 50PPM 0204 0.4 W

TE Part # 9-2176316-4
MELF SMA-A 330K 1% 50PPM 0207 1W

Customers Also Bought

TE Part #1-215309-0
2X10P HV100 REC CON. TE, 8.5MM

TE Part #1419108-1
RT114012

TE Part #215309-2
2X2P HV100 REC CON. TE, 8.5MM

TE Part #1-925017-0
250 FASTON HSG.,REC.,1 POS, NATRUAL

TE Part #1658526-5
609-1041LF FEM SOCKT,LEAD FREE

TE Part #2007779-1
IMP100S,H,V3P10C,LG,REW39,4.5

TE Part #1-215079-6
FEMALE-ON-BOARD CONNECTOR TOP ENTRY

TE Part #Y5015-000000100020
PLUG WITH RFI GROUNDING - FEMALE - CIRH

TE Part #1622719-1
LR2 1% 24R

Documents



Product Drawings

MELF SMA_A 6K8 1% 50PPM 0204 0.4W

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-2176315-0_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-2176315-0_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-2176315-0_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMA-A-1017

English