

Alcoswitch

TE Internal #: 7-1437622-6

Switch Knobs, Knob, Aluminum, Straight Knurl Knob Design, .25in [6.35mm] Shaft Size, .5in [12.7mm] Switch Knob Diameter, Black

/Natural, Arrowhead

View on TE.com >



Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**Switch Knob Material: **Aluminum**

Knob Design: Straight Knurl Shaft Size: 6.35 mm [.25 in]

Switch Knob Diameter: 12.7 mm [.5 in]

Features

Product Type Features

Switch K	Knob Product Type	Knob	

Configuration Features

Skirt	With
Spinner	Without
Spin Plate	Without
Knob Design	Straight Knurl

Body Features

Switch Knob Material	Aluminum
Switch Knob Color	Black/Natural

Dimensions

Shaft Size	6.35 mm[.25 in]
Switch Knob Diameter	12.7 mm[.5 in]

Identification Marking

Indicator Style	Arrowhead
Indicator Location	On Skirt

Other

Comment	Body Black, Top Natural



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Pb (.6% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts







Customers Also Bought







TE Part #1658620-3 16 NOVO MIL 15DP, LEAD FREE



TE Part #1-5530843-0 CONN SEC II 43 POS 100C/L





TE Part #1-643077-2 Nylon PCB Connector Covers: 2.54 mm, MTA 100



TE Part #1-6609000-0 CORCOM EEA SERIES IEC FILTERED **INLETS**



TE Part #1437623-4 KS500B1/4=KNOB BLK W/SKIRT 1/4



TE Part #1-1986720-2 STR PLUG SPRING TYPE RH 12P, 3.81 mm



FUNCTION INLET FIL

TE Part #ZPF000000000097341 768-0319-37 E

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1437622-6_99_c-7-1437622-6-99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1437622-6_99_c-7-1437622-6-99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1437622-6_99_c-7-1437622-6-99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use

Datasheets & Catalog Pages

Alcoswitch Products

English