

Alcoswitch

TE Internal #: 7-1437624-5

Switch Knobs, Knob, Phenolic, Straight Knurl with Bar Pointer Knob

Design, .125in [3.17mm] Shaft Size, .52in [13.2mm] Switch Knob

Diameter, Black
View on TE.com >



Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**Switch Knob Material: **Phenolic**

Knob Design: Straight Knurl with Bar Pointer

Shaft Size: 3.17 mm [.125 in]

Switch Knob Diameter: 13.2 mm [.52 in]

Features

Product Type Features

Switch Knob Product Type

| Configuration Features | |
|------------------------|---------------|
| Spin Plate Style | Spun Aluminum |
| Skirt | Without |
| Spinner | Without |
| Spin Plate | With |

Knob

Straight Knurl with Bar Pointer

Body Features

Knob Design

| Switch Knob Material | Phenolic |
|----------------------|----------|
| Switch Knob Color | Black |

Dimensions

| Shaft Size | 3.17 mm[.125 in] |
|----------------------|------------------|
| Switch Knob Diameter | 13.2 mm[.52 in] |

Identification Marking

| Indicator Style | Line |
|--------------------|------------|
| Indicator Location | Top & Side |

Product Compliance



For compliance documentation, visit the product page on TE.com>

| EU RoHS Directive 2011/65/EU | Compliant |
|---|---|
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Customers Also Bought







Alignment

















Documents

Product Drawings

PKJ50B1/8=KNOB PLASTIC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1437624-5_B_c-7-1437624-5-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1437624-5_B_c-7-1437624-5-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1437624-5_B_c-7-1437624-5-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English