



Passive Components > Inductors > High Frequency & RF Inductors



Inductor Type: **High Frequency**
Termination Method to Printed Circuit Board: **Surface Mount**
Packaging Method: **Taped & Reeled**
Passive Component Dimensions: **1.8 x 1.12 x 1.02 mm**
Passive Component Tolerance: **5 %**

Features

Product Type Features

Inductor Type	High Frequency
Element Type	Wire Wound
Package Size Code	0603

Electrical Characteristics

Self Resonant Frequency	4.8 GHz
Passive Component Tolerance	5 %
Inductance	.0075 μ H
Current Rating (Max)	700 mA
DC Resistance	.11 Ω

Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Dimensions

Passive Component Dimensions	1.8 x 1.12 x 1.02 mm
------------------------------	----------------------

Usage Conditions

Operating Temperature Range	-40 – 125 $^{\circ}$ C, -40 – 125 $^{\circ}$ C
-----------------------------	--

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------



Other

Inductor Quality Factor	27
-------------------------	----

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 1624112-8 3650 0603 68nH 5% 2K RL	 TE Part # 6-1624113-2 3650 2A 0.56uH 5% 2K RL	 TE Part # 4-1624112-4 3650 0402 16nH 5% 2K RL	 TE Part # 5-1624113-2 3650 2A 0.22uH 5% 2K RL
---	---	---	---






TE Part # 4-1879023-8
3650 1008 10uH 5% 2K RL

Also in the Series | Sigma 3650



High Frequency & RF Inductors(270)


Customers Also Bought



TE Part #1-1625999-1
Power Resistors: Aluminum Housed, HSC



TE Part #T4145435041-001
M12 Panel Mount PCB



TE Part #1735042-6
1MM FFC SMT V ASSY 6P EMBOSS



TE Part #1-1624112-9
3650 0402 3.6nH 5% 2K RL



TE Part #1624112-2
3650 0603 12nH 5% 2K RL



TE Part #1879417-5
CPF0603 750K 0.1% 25PPM 5K RL



TE Part #1-215460-2
MICRO-MATCH FEM.SE



TE Part #1622264-1
LR0204 1% 62K



TE Part #1-1624112-8
3650 0402 3.3nH 5% 2K RL



TE Part #1622363-5
LR1 1% 1K78



Documents

Product Drawings

3650 0603 7.5nH 5% 2K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1624112-0_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1624112-0_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1624112-0_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Low Inductance, High Frequency Chip Inductors - Type 3650 Series

English