

KNS701BA1/4 ✓ ACTIVE

Alcoswitch

TE Internal #: 8-1437622-0

Switch Knobs, Knob, Aluminum, Straight Knurl Knob Design, .25in [6.35mm] Shaft Size, .75in [19.1mm] Switch Knob Diameter, Black /Natural, Arrowhead

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**

Switch Knob Material: **Aluminum**

Knob Design: **Straight Knurl**

Shaft Size: **6.35 mm [.25 in]**

Switch Knob Diameter: **19.1 mm [.75 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	With
Spinner	Without
Spin Plate	Without
Knob Design	Straight Knurl

Body Features

Switch Knob Material	Aluminum
Switch Knob Color	Black/Natural

Dimensions

Shaft Size	6.35 mm[.25 in]
Switch Knob Diameter	19.1 mm[.75 in]

Identification Marking

Indicator Style	Arrowhead
Indicator Location	On Skirt

Other

Comment	Body Black, Top Natural
---------	-------------------------



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #1558660-1
PCB Power Relay: 30 amp, Monostable
DC



TE Part #1676979-4
TW 1W 10K 6.35X25PL



TE Part #1649341-8
T9CP1A54-24



TE Part #104503-9
10 MTE PIN HSG SR RIB .100CL



TE Part #1437624-9
PK90B1/4=KNOB PLASTIC BLK 1/4



TE Part #1676673-1
RN 0805 24R3 0.1% 10PPM CUT
LENGTH



TE Part #1658610-4
IDC D-Sub: Receptacle Assembly, Low
Profile, Signal, 2.77 mm



TE Part #EC0610-000
Z-TYPE PUSH-ON MARKERS



TE Part #1-5530843-8
CONN SEC II 30 POS 100C/L



TE Part #1-2176078-1
EP 1W 470R 5%

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_8-1437622-0_99_c-8-1437622-0-99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-1437622-0_99_c-8-1437622-0-99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-1437622-0_99_c-8-1437622-0-99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English