

### **Alcoswitch**

TE Internal #: 9-1437622-2

Switch Knobs, Knob, Aluminum 5056, Straight Knurl with Bar Pointer Knob Design, .25in [6.35mm] Shaft Size, .5in [12.7mm]

Switch Knob Diameter, Black

View on TE.com >



Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob** 

Switch Knob Material: Aluminum 5056

Knob Design: Straight Knurl with Bar Pointer

Shaft Size: 6.35 mm [ .25 in ]

Switch Knob Diameter: 12.7 mm [.5 in]

## **Features**

## **Product Type Features**

Switch Knob Product Type	Knob	
Configuration Features		

Skirt	Without
Spinner	Without
Spin Plate	Without

Knob Design Straight Knurl with Bar Pointer

### **Body Features**

Switch Knob Material	Aluminum 5056
Switch Knob Color	Black

### **Dimensions**

Shaft Size	6.35 mm[.25 in]
Switch Knob Diameter	12.7 mm[.5 in]

## **Identification Marking**

Indicator Style	Line
Indicator Location	Side

## **Product Compliance**

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Pb (.6% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# Compatible Parts



# Customers Also Bought





TE Part #1-1676814-2
Power Resistors: Aluminum Housed,
HSA




TE Part #1-87499-8
10 MODIV HSG COMP SR .100CL



TE Part #1879628-4 H4P 180K 1% 100PPM





TE Part #1-1879665-1 H8 15K8 0.1% 15PPM



TE Part #1-6609035-3
CORCOM SK SERIES SINGLE PHASE
FILTERS



TE Part #1-2273046-1 M12 A-CODE MALE STRAIGHT PIGTAIL



TE Part #YDTS20F17-35PNV001 D38999: Square Flange, 17-35 insert





## **Documents**

### **CAD Files**

3D PDF

3D

**Customer View Model** 

ENG\_CVM\_CVM\_9-1437622-2\_A\_c-9-1437622-2-a.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_9-1437622-2\_A\_c-9-1437622-2-a.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_9-1437622-2\_A\_c-9-1437622-2-a.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use

Datasheets & Catalog Pages

**Alcoswitch Products** 

English