



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **General Purpose Resistor**

Number of Terminations: **2**

Package Size Code: **0402**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	General Purpose Resistor
Package Size Code	0402
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	50 V
Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	91 Ω
Power Rating	.063 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	1 x .5 x .35 mm
------------------------------	-----------------

Usage Conditions



Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Pb (2.02% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRG0402F91R

Neohm CRG, Surface Mount Resistors, General Purpose Resistor, 2 Termination, 0402, Taped & Reeled, 1 %, Thick Film, Resistance Class Up to 1kΩ, 91 Ω



TE Part # 1623097-1
[CRG0805 1% 10K](#)

TE Part # 1623404-1
[CRG1206 1% 10K](#)

TE Part # 1622829-1
[CRG0603 1% 10K](#)

TE Part # 1676480-1
[CRG0402 1% 100K](#)

TE Part # 1-1622826-8
[CRG0402 5% 1K0](#)

Also in the Series | [Neohm CRG](#)

[Surface Mount Resistors\(647\)](#)

Customers Also Bought

TE Part #1658538-2
[D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20](#)

TE Part #1658540-1
[D-Sub Connector Contacts: Pin, Brass, Signal, Size 20](#)

TE Part #1-284392-0
[TERMI-BLOK PCB SIDE ENTRY STAC](#)

TE Part #1-2176177-5
[CRGH0603 1% 2K2 0.2W](#)

TE Part #1-2176337-3
[CRGCO 0402 100R 1%](#)

TE Part #1-2176337-5
[CRGCO 0402 150R 1%](#)

TE Part #1-2176337-0
[CRGCO 0402 56R 1%](#)

TE Part #1-2176337-1
[CRGCO 0402 68R 1%](#)



Documents

Product Drawings

CRG0402 1% 91R

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-1622826-8_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-1622826-8_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-1622826-8_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Thick Film Chip Resistors - Type CRG series

English