



Passive Components > Resistors > Through-Hole Resistors > Wirewound Resistor: Vertical Mount



Resistor Type: **Power Resistor**

Passive Component Dimensions: **20 x 7 x 8 mm**

Number of Terminations: **2**

Packaging Method: **Loose Piece - Box**

Passive Component Tolerance: **10 %**

[All Wirewound Resistor: Vertical Mount \(166\)](#)

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	10 %
Resistance Class	Up to 1kΩ
Resistance Value	2.2 Ω
Power Rating	4 W

Body Features

Passive Component Lead Type	Axial-Leaded
-----------------------------	--------------

Termination Features

Number of Terminations	2
Passive Component Termination Material Type	Tinned Copper Leads

Dimensions

--



Passive Component Dimensions	20 x 7 x 8 mm
------------------------------	---------------

Usage Conditions

Operating Temperature Range	-55 – 350 °C
Temperature Coefficient	±400 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C339-SB19B
Wirewound Resistor: Vertical Mount

TE Part # CAT-C339-SB19
Wirewound Resistor: Axial Mount, 17 Watt

Also in the Series | CGS SBC

Surface Mount Resistors(1)

Through-Hole Resistors(207)

Customers Also Bought

TE Part #1-1623730-7
Wirewound Resistor: Vertical Mount

TE Part #1622298-1
LR1 1% 10K

TE Part #1622461-1
LR1 1% 3K3

TE Part #1622500-1
LR1 1% 4K7

TE Part #1393215-6
V23057-A0002-A201

TE Part #1622392-1
LR1 1% 22R

TE Part #1-1623714-7
FCB4 2R2 5% HP

TE Part #1-967325-1
CIRCULAR DIN HOUSINGS

TE Part #929974-1
ROUND CONNECTOR SYSTEM, PIN AND SOCKET

TE Part #1-1393225-7
RY611005



Documents

Product Drawings

BCHE 4 W 2R2 10%

English

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

High Power Resistor - Type SBC (Square Ceramic) Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English