



Corcom DC

TE Internal #: 3-6609074-4

TE Internal Description: 100DCB6F J0=F7928

CORCOM DC SERIES DC FILTERS

[View on TE.com >](#)



[All CORCOM DC SERIES DC FILTERS \(15\)](#)

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [Corcom DC](#)



DC Filters(15)


## Customers Also Bought



TE Part #1705950-1  
RJ25 Connectors



TE Part #5-1879359-8  
RN 0603 200R 0.1% 10PPM CUT LENGTH




TE Part #2-1586044-0  
20P VAL-U-LOK R/A HDR SCRMT V0




TE Part #3-641149-5  
05P MTA156 ASSY 20AWG YEL LF



TE Part #5-103167-3  
12 MODII HDR DRRA SHRD LF



TE Part #1-1744418-6  
16 POS EP 2.5 HDR, GLOW WIRE



TE Part #1776253-8  
R/A Top Wire Entry, 3.5mm, HT,



TE Part #3-641523-4  
04P MTA156 POST CON ASSY LF



TE Part #5-103330-2  
04 MODII HDR DRRA B/A .100 CL LF



TE Part #ZPF000000000008615  
983-6S 14-15 SN-L

## Documents

[Product Drawings](#)  
100DCB6F J0=F7928

English

### CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_3-6609074-4\\_O.2d\\_dxf.zip](#)



English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_3-6609074-4\\_O.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_3-6609074-4\\_O.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[1654001\\_CORCOM\\_PRODUCT\\_GUIDE](#)

English

[1654001\\_Corcom\\_Product\\_Guide\\_DC\\_Series](#)

English

[1-1654250-1\\_CORCOM\\_EMI\\_RFI\\_QRG](#)

English

[Corcom Combined Selector Charts](#)

English