

CBT50J5R1 x OBSOLETE

Neohm CBT

TE Internal #: 7-1625876-1

TE Internal Description: CBT 1/2 5% 5R1

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [Neohm CBT](#)




Through-Hole Resistors(66)


Customers Also Bought



TE Part #1-2314102-1
M12 CRIMP CONTACT FOR D AND A5



TE Part #5-1630186-7
Power Resistors: Aluminum Housed, HSA



TE Part #2351885-2
2POS TB HDR 180 DEG, PITCH 5.0&TL 4.5mm



TE Part #2176399-8
3502 1K0 5%



TE Part #3-2176348-9
CRGCQ 2010 2M2 5%



TE Part #9-2176378-0
RQ 0805 84R5 0.1% 10PPM 5K RL



TE Part #2-1415899-0
PCB Power Relay: 12-16 Amp, Monostable



TE Part #641643-2
Connector Contact: Socket /Receptacle, Wire-to-Board / Wire-to-Wire, MTA 100



TE Part #8-35216-1
PIDG SLOTTED RING TONGUE TERMINALS



TE Part #C145614001
VERSAFLEX-03-0-SP

Documents

Product Drawings

CBT 1/2 5% 5R1

English

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

Carbon Composition Resistors - Type CBT Series

English



8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English